



LOC	DIST	REV	DATE	APPD
G	14			

ZONE	LTR	DESCRIPTION	DATE	APPD
A		REVISED PER 0720-0230-93	2/28/94	DAV

METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE 22-16 AWG STRANDED	UL E13288 Listed 22-16 AWG STRANDED
LR7189 Certified NOT CERTIFIED	MILITARY P/N AND CLASS NOT APPLICABLE

△ STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928, COMMERCIAL WIRE RANGE IS 22-16



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
0.26-1.65mm² [509-3,260] CIR MILS
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING DEPARTMENT
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm - FINISHES -
TOLERANCES ON:
2 PLG DEC ±
3 PLG DEC ±
ANGLES ±

MATERIAL
COPPER PER
ASTM B-152
ANNEALED

FINISH
TIN PLATE
0.00254 [0.000100] MIN
THK PER MIL-T-10727

DR 2-4-93
TA BRINKMAN
CHK 2-4-93
DA PATTERSON
APPD 2-4-93
DE MILLER
APPD 2-4-93
JL NECKLEY
PRODUCT SPEC

AMP
AMP Incorporated
Harrisburg, PA 17105-3508

TERMINAL, RING TONGUE,
BUDGET

APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
-	G	00779	G-324124
WEIGHT -	SCALE 8:1		SHEET 1 OF 1