



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.


FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	SIGNAL				POWER					E1				
		E2	3	2	1	P5	P4	P3	P2	P1					
51915-048	D C B A		H	H	X	G	G	X	F	F	X	E	E	X	
															



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
E	N/A [N/A]	SIGNAL
F	N/A [N/A]	SIGNAL
G	N/A [N/A]	SIGNAL
H	N/A [N/A]	SIGNAL
PA	.042 [1.07]	POWER
X	OMITTED	OMITTED

mat'l code SEE NOTE 2				tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com	
ltr	ecn no.	dr	date	linear	.XX±.01/0.X±0.3		COPY		
A	V04-0503	TAB	05/13/04		.XXX±.005/0.XX±0.13		projection		
					.XXXX±.0020/0.XXX±0.051				
				angles	0°±2°		title		
				dr	T. BRUNGARD	05/13/04	5P + 12S		
				engr	M. GRAY	05/13/04	R/A SOLDER RECEPTACLE		
				chr	M. GRAY	05/13/04	product family		
				appd	M. GRAY	05/13/04	PwrBlade		
sheet index		revision		A	A	A	code		
		sheet		1	2	3	213		
							sheet		
							1 of 4		

cage code 22526





Pro/E

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51915-048



mat'l code SEE NOTE 2				tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com			
ltr	ecn no.	dr	date	linear	.XX±.01/0.X±0.3	COPY		title 5P + 12S R/A SOLDER RECEPTACLE			
A					.XXX±.005/0.XX±0.13	projection		product family PwrBlade			
					.XXXX±.0020/0.XXX±0.051	INCH/MM		code 213			
				angles	0° ± 2°	scale		size A			
				dr	T. BRUNGARD 05/13/04	1:1		sheet 2 of 4			
				enrg	M. GRAY 05/13/04						
				chr	M. GRAY 05/13/04						
				appd	M. GRAY 05/13/04						
sheet index		revision sheet									

Pro/E

3

cage code
22526

4

PDM: Rev:A

STATUS: **Released**


Printed: Dec 20, 2010


Tous droits strictement réservés. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51915-048



mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com	
ltr	ecn no.	dr	date	linear	.XX±.01/0.X±0.3		COPY		projection 	title	
A					.XXX±.005/0.XX±0.13					5P + 12S	
					.XXXX±.0020/0.XXX±0.051					R/A SOLDER RECEPTACLE	
				angles	0°±2°				INCH/MM 	product family	
				dr	T. BRUNGARD	05/13/04	PwrBlade			code	
				enrg	M. GRAY	05/13/04	size			213	
				chr	M. GRAY	05/13/04	dwg no			sheet	
				appd	M. GRAY	05/13/04	scale		A	51915-048	3 of 4
sheet index		revision sheet									

Pro/E

cage code 22526

PDM: Rev:A

STATUS: Released

Printed: Dec 20, 2010

PRODUCT NUMBER
51915-048

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH
ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

2. HOUSING MATERIAL: UL 94 V-0 GLASS FILLED

HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY

3. PLATING:
SIGNAL PINS: 30u"/0.76um Au OVER 50u"/1.27um Ni
POWER CONTACTS: 50u"/1.27um Ni UNDER ALL
WITH 30u"/0.76um Au ON CONTACT AREA
AND SnPb ON PCB INTERFACE

4. MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON
THIS SURFACE.

5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.

6. PACKAGED IN TRAYS.

PCB NOTES:


7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.

8. MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.

9. $\varnothing .0453 \pm .0010$ [1.151 $\pm$ 0.025] DRILLED HOLES PLATED WITH
.0003 [0.008] MIN SnPb OVER .001 [0.03]
TO .003 [0.08] Cu PLATING TO ACHIEVE
 $\varnothing .040 \pm .003$ [1.02 $\pm$.07] HOLE.

10. "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.

11. CONNECTOR KEEP-OUT ZONE.

mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
ltr	ecn no.	dr	date	linear	.XX $\pm$.01/0.X $\pm$ 0.3		COPY		 INCH/MM		
A					.XXX $\pm$.005/0.XX $\pm$ 0.13		projection				
					.XXX $\pm$.0020/0.XXX $\pm$ 0.051		scale				
				angles	0° $\pm$ 2°						
				dr	T. BRUNGARD	05/13/04	1:1		product family		code
				enrg	M. GRAY	05/13/04			PwrBlade		213
				chr	M. GRAY	05/13/04			size		sheet
				appd	M. GRAY	05/13/04			A		4 of 4
sheet index		revision sheet									