




- 1 $0.38\mu\text{m}$ [$.000015$] MIN GOLD ON MATING AREA,
 $1.27\mu\text{m}$ [$.000050$] MIN BRIGHT TIN-LEAD ON CRIMP AREA, BOTH OVER
 $1.27\mu\text{m}$ [$.000050$] MIN NICKEL.
- 2 $2.54\mu\text{m}$ [$.000100$] MIN BRIGHT TIN-LEAD, OVER
 $1.27\mu\text{m}$ [$.000050$] MIN NICKEL.
- 3 GOLD FLASH ON CRIMP AREA,
 $2.54\mu\text{m}$ [$.000100$] MIN TIN ON MATING AREA, BOTH OVER
 $1.27\mu\text{m}$ [$.000050$] MIN NICKEL.
- 4 $0.38\mu\text{m}$ [$.000015$] MIN GOLD ON MATING AREA,
GOLD FLASH ON CRIMP AREA, BOTH OVER
 $1.27\mu\text{m}$ [$.000050$] MIN NICKEL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 6 GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL

5 OBSOLETE	4	487923-5-
3	6	487923-4
5 OBSOLETE	1	487923-3-
	2	487923-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 3-7-90	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R.STONE 3-8-90				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC ± -		CONTACT, SOLDER TAB, .050 C/L			
	1 PLC ± -		-			
	2 PLC ± 0.13 [.005]		-			
MATERIAL		FINISH	WEIGHT	SIZE	CAGE CODE	DRAWING NO
PHOSPHOR BRONZE		SEE TABLE	-	A2	00779	C=487923
CUSTOMER DRAWING			SCALE	SHEET	REV	RESTRICTED TO
			10:1	1 OF 1	D1	-