


CATALOG LISTING
622EN230
PAGE 1 OF 1
RELEASE NO. PR-23406
REPLACES

ISSUE
M
2


REVISIONS
A PR-REL
PR23406
JK
11 MAY 98



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH


CHARACTERISTICS
DRAWN
L J K 11 MAY 98
DDM/CAD
OPERATING FORCE ----- 6 - 12 LB
FULL OVERTRAVEL FORCE --- 30 LB MAX
RELEASE FORCE ----- 4 LB MIN
PRETRAVEL ----- .040 MAX
DIFFERENTIAL TRAVEL ----- .020 MAX
OVERTRAVEL ----- .125 MIN

CHARACTERISTICS		ELECTRICAL DATA		THIRD ANGLE PROJECTION	
		CONTACT ARRANGEMENT 2X SPDT 7			
LOAD	28 VDC		DO NOT SCALE PRINT UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
	SEA LEVEL	50,000 FT.			
RES	1	1	ONE PLACE (.0) ± .030		
IND	0.5	0.5	TWO PLACE (.00) ± .015		
			THREE PLACE (.000) ± .005		
			ANGLES ±		
			WEIGHT		



NOTES

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 4
- 3 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
- 4 - CIRCUIT DIAGRAM, AND CATALOG LISTING SHOWN ON NAMEPLATE
- 5 - TO ADJUST ROLLER DIRECTION, REMOVE LOCK NUT, SCREW, AND ROLLER. DEPRESS PLUNGER UNTIL IT CAN BE ROTATED TO DESIRED POSITION. RETURN PLUNGER TO FREE POSITION AND REASSEMBLE ROLLER
- 6 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805
- 7 - BIFURCATED GOLD CONTACT BASIC SWITCHES



CIRCUIT DIAGRAM

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[622EN230](#)