






13
-2 WAS CPB3-51592-2
C
B
A

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
			D	RELEASE DRAWING PER TTI 82-118	7-23-82
A			A	ADDED -2 PER TTI 83-133	11-1-83
			A1	RESTORATION	8-3-85
			B	REV PER ECN CM 705	12-1-86
			C	REV PER EC 0730-0201-94	4-26-95
				APPROVED	



ASSEMBLY DETAILS

- 1 SHEET METAL SCREWS NOT SUPPLIED
- 2 TWO REQUIRED PER CONNECTOR.
- 3 MAX WIRE BUNDLE WITHOUT INSERT IS 6 AT .190 DIA. AND MIN WIRE BUNDLE WITH INSERT IS 6 AT .040 DIA.
- 4 STYLE II DOES NOT INCLUDE INSERT.
- 5 DETACHABLE INSERT MAY SEPARATE FROM STRAIN RELIEF BODY DURING SHIPPING.

NYLON 94 V-O	II	643313-2
NYLON 94 V-O	I	643313-1
MATERIAL	STYLE	PART NO.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS $\pm .015$ ANGLES $\pm$	CONTRACT NO	AMP AMP INCORPORATED Harrisburg, Pa. 17105		
	DP <i>M. Fehr</i> 7-23-82			
	CHK <i>D. Heide</i> 10/1/82			
	APPD <i>G. E. Quella</i> 11/1/82			
MATERIAL SEE TABLE	DSGN APPD	NAME STRAIN RELIEF AND INSERT, UNIVERSAL MATE-N-LOK™ 6 CIRCUIT		
FINISH SEE TABLE	OTHER APPD	SIZE C		
	FSCM NO 00779	DRAWING NO 643313		
	SCALE 2:1	SHEET 1 OF 1		