





LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
			A15	REVISED PER ECR-15-012073	13AUG2015	NK	W W	
			A17	ECR-16-016334	17NOV2016	FV	RR	
			A18	ECR-17-009651	19JUL2017	RS	DC	




SCALE 5:1



- 1 WIRE RANGE : STRANDED 0.22-0.35 mm² (INS. DIA. 1.30±0.1)
- 2 MATING PART: TAB HEADER P/N 829866;
PCB FRAME P/N 964575 (PCB THK 1.5±0.14 COPPER CLADDING INCLUDED)
SEE PRODUCT SPEC. 108-18056 FOR FRAME APPLICATION

- 3 KEYING RIBS TO BE REMOVED BY TERMINATION MACHINE
- 4 CUT OFF DIMENSION DUE TO PRODUCTION PROCESS
- 5 CIRCUIT No. IDENTIFICATION
- 6 TE TRADEMARK (OPTIONAL POSITION)
- 7 TAMPOGRAPHIC COLOUR CODE AREA
(P/NS IDENTIFICATION BEFORE CRIMPING)
- 8 POLARIZATION RIB BETWEEN CAVITIES.
(SEE BELOW TYPICAL POLARIZATION CUTOFF ON PCB)



- 9 PRELIMINARY PART NOT RELEASED FOR PRODUCTION.

- 10 X - CAVITY LOADED WITH CONTACT
O - CAVITY WITHOUT CONTACT
- 11 PBT GF
- 12 PBT GF, UL94-V0 & GWEP7 750 NO-FLAME,
NATURAL

P/N 0-284932-3 AS SHOWN

BLACK	FULLY LOADED										2/3	13	30.0	34.9	4-284932-3	1-2311501-3	413				
GREEN					X	X	0	X	0	X	4/5	6	12.5	17.4	3-284932-6	2311505-6					
BLUE	FULLY LOADED																		1-284932-6	4-2311500-6	
BLACK	FULLY LOADED										9/10	11	25.0	29.9	1-284932-1	1-2311501-1					
BLACK	FULLY LOADED										7/8	10	22.5	27.4	1-284932-0	2-2311500-0					
BLACK	FULLY LOADED										2/3	9	20.0	24.9	0-284932-9	2311500-9					
BROWN	FULLY LOADED										2/3	8	17.5	22.4	2-284932-8	3-2311500-8					
BLACK	FULLY LOADED										1/2 and 7/8				0-284932-8	2-2311500-8					
RED	FULLY LOADED										2/3	7	15.0	19.9	0-284932-7	1-2311500-8					
BLACK	FULLY LOADED										1/2	6	12.5	17.4	2-284932-6	3-2311500-6					
RED	FULLY LOADED										2/3				0-284932-6	2-2311500-6					
RED	FULLY LOADED										4/5	5	10.0	14.9	3-284932-5	5-2311500-5					
GREEN	FULLY LOADED										3/4				2-284932-5	4-2311500-5					
BROWN	FULLY LOADED										2/3				4-284932-5	3-2311500-5					
BLACK												0-284932-5	2-2311500-5								
BLACK	FULLY LOADED										3/4	4	7.5	12.4	2-284932-4	4-2311500-4					
BROWN	FULLY LOADED										1/2				0-284932-4	3-2311500-4					
RED	FULLY LOADED										2/3	3	5.0	9.9	3-284932-3	6-2311500-3					
GREEN															2-284932-3	5-2311500-3					
BLACK	FULLY LOADED										1/2				0-284932-3	4-2311500-3					
COLOUR CODE	7	11	10	9	8	7	6	5	4	3	2	1	POLARIZ. RIB	8	HSG POS	DIM.A	DIM.B	TE P/N	11	TE P/N	12

-	-	-	-	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. FABRIS CHK -	27FEB2004	 TE Connectivity										
SEE TABLE	PH. BRONZE, TIN PLATED	IDC RECEPTACLE CONTACT	2		DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±1°	APVD G. TURCO 27FEB2004	NAME	DUOPLUG 2.5 FEMALE CONNECTOR STANDARD VERSION, KEYED (FULLY LOADED)									
	PBT GLASS FIBER FILLED	FEMALE HOUSING	1															
Q.TY	MATERIAL	DESCRIPTION	ITEM						SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO						
1	REVISIONE DELL'ASSEMBLATO (REVISION OF EACH ASSY NO)			MATERIAL SEE TABLE		FINISH		WEIGHT	A1	00779	C=284932	-						
ELENCO DEI COMPONENTI (PARTS LIST)									CUSTOMER DRAWING		SCALE	10:1	SHEET	1	OF	1	REV	A18
Q.TY PER ASSEMBLATO (QTY REQ'D PER ASSY)																		