

Technical Data Sheet

0805 Package Chip LED (1.0mm Height)

17-21UBC/C430/TR8

Features

- Package in 8mm tape on 7" diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Mono-color type.
- Pb-free.
- The product itself will remain within RoHS compliant version.

Descriptions

- The 17-21 SMD LED is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

Applications

- Backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.

Device Selection Guide


D	Chip		Resin Color	
Part No.	Material	Emitted Color		
17-21UBC/C430/TR8	InGaN/SiC	Blue	Water Clear	





Everlight Electronics Co., Ltd. http://www.everlight.com Rev.2 Page: 1 of 9

Device No: DSE-171-018 Prepared date: 7-Apr-2009 Prepared by: Huang yongxin


Package Outline Dimensions








For reflow soldering (Propose)





Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

 $Everlight\ Electronics\ Co.,\ Ltd.$

Device No: DSE-171-018

http://www.everlight.com Prepared date: 7-Apr-2009 Rev.2

Page: 2 of 9

Prepared by: Huang yongxin

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit	
Reverse Voltage	V_R	5	V	
Forward Current	I_{F}	30	mA	
Peak Forward Current (Duty 1/10 @1KHz)	$ m I_{FP}$	70	mA	
Power Dissipation	Pd	130	mW	
Electrostatic Discharge(HBM)	ESD	1000	V	
Operating Temperature	T _{opr}	-40 ~ +85	$^{\circ}\!\mathbb{C}$	
Storage Temperature	T_{stg}	-40 ~ +90	$^{\circ}\!\mathbb{C}$	
Soldering Temperature	T _{sol}	Reflow Soldering: 260 °C for 10 sec. Hand Soldering: 350 °C for 3 sec.		

Electro-Optical Characteristics (Ta=25°C)

		•	•				
Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition	
Luminous Intensity	Iv	16	20		mcd		
Viewing Angle	$2 heta_{ ext{1/2}}$		140		deg		
Peak Wavelength	λρ		428		nm		
Dominant Wavelength	λd		466		nm	$I_F = 5mA$	
Spectrum Radiation Bandwidth	Δλ		65		nm		
Forward Voltage	V_{F}		3.8	4.5	V		
Reverse Current	I_R			50	μ A	V _R =5V	


Everlight Electronics Co., Ltd. http://www.everlight.com Rev.2 Page: 3 of 9


Device No: DSE-171-018 Prepared date: 7-Apr-2009 Prepared by: Huang yongxin


Relative luminous intensity (%)


17-21UBC/C430/TR8


Typical Electro-Optical Characteristics Curves























Everlight Electronics Co., Ltd.

Device No: DSE-171-018

http://www.everlight.com Prepared date: 7-Apr-2009 Rev.2

Page: 4 of 9


Prepared by: Huang yongxin

Label explanation


CAT: Luminous Intensity Rank

HUE: Dom. Wavelength Rank

REF: Forward Voltage Rank



Reel Dimensions




Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

Everlight Electronics Co., Ltd. http://www.everlight.com Rev.2 Page: 5 of 9


Device No: DSE-171-018 Prepared date: 7-Apr-2009 Prepared by: Huang yongxin

Carrier Tape Dimensions: Loaded quantity 3000 PCS per reel



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

Moisture Resistant Packaging



Everlight Electronics Co., Ltd. http://www.everlight.com Rev.2 Page: 6 of 9

Device No: DSE-171-018 Prepared date: 7-Apr-2009 Prepared by: Huang yongxin



Reliability Test Items And Conditions

The reliability of products shall be satisfied with items listed below.

Confidence level: 90%

LTPD: 10%

No.	Items	Test Condition	Test Hours/Cycles	Sample Size	Ac/Re
1	Reflow Soldering	Temp. : 260°C±5°C Min. 5sec.	6 Min.	22 PCS.	0/1
2	Temperature Cycle	$H: +100^{\circ}\mathbb{C}$ 15min $\int 5 \text{ min}$ $L: -40^{\circ}\mathbb{C}$ 15min	300 Cycles	22 PCS.	0/1
3	Thermal Shock	$H: +100^{\circ}\mathbb{C}$ 5min $\int 10 \sec$ $L: -10^{\circ}\mathbb{C}$ 5min	300 Cycles	22 PCS.	0/1
4	High Temperature Storage	Temp. : 100°℃	1000 Hrs.	22 PCS.	0/1
5	Low Temperature Storage	Temp. : -40°C	1000 Hrs.	22 PCS.	0/1
6	DC Operating Life	$I_{\scriptscriptstyle F}=20\;mA$	1000 Hrs.	22 PCS.	0/1
7	High Temperature / High Humidity	85°C / 85% RH	1000 Hrs.	22 PCS.	0/1

Everlight Electronics Co., Ltd. http://www.everlight.com Rev.2 Page: 7 of 9

Device No: DSE-171-018 Prepared date: 7-Apr-2009 Prepared by: Huang yongxin

Precautions For Use


1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
 - 2.1 Do not open moisture proof bag before the products are ready to use.
 - 2.2 Before opening the package: The LEDs should be kept at 30° C or less and 90%RH or less.
 - 2.3 After opening the package: The LED's floor life is 1 year under 30℃ or less and 60% RH or less. If unused LEDs remain, it should be stored in moisture proof packages.
 - 2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.

Baking treatment : $60\pm5^{\circ}$ C for 24 hours.

- 3. Soldering Condition
- 3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

Everlight Electronics Co., Ltd. http://www.everlight.com Rev.2 Page: 8 of 9

Device No: DSE-171-018 Prepared date: 7-Apr-2009 Prepared by: Huang yongxin




4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350° C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



EVERLIGHT ELECTRONICS CO., LTD.

Office: No 25, Lane 76, Sec 3, Chung Yang Rd, Tucheng, Taipei 236, Taiwan, R.O.C Tel: 886-2-2267-2000, 2267-9936

Fax: 886-2267-6244, 2267-6189, 2267-6306

http://www.everlight.com

Everlight Electronics Co., Ltd. http://www.everlight.com Rev.2 Page: 9 of 9

Device No: DSE-171-018 Prepared date: 7-Apr-2009 Prepared by: Huang yongxin