






NOTES:

1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FDR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. OPERATING FORCE: 425±100 CM/STANDARD
6. OPERATING TEMP: -30° to 85°C
7. CIRCUIT SP: 2 POSITIONS, 90° INDEX.
8. DIELECTRIC STRENGTH: 1000V RMS min. @Seq Level
9. HARDWARE SUPPLIED ON SWITCH- SEE BELOW
STOP RING, LOCKWASHER, & HEXNUT
10. ▲ DENOTES CRITICAL PARAMETER.



CONTACT CONFIGURATION
(BBM)



TERMINATION DETAIL
SCALE 2X

TITLE			
KC54A10.001NLS			
E-SWITCH®			
A	13082	RELEASED FOR PRODUCTION	4/24/03
REV.	ECN No.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE 1.5:1			
DATE 4/24/03			
DR AR			
DWG G527562			
REV A			