




- **SAW Frequency Stabilization**
- **Fundamental-Mode Oscillation at 1000.0 MHz**
- **A Rugged, Compact General-Purpose Oscillator**
- **Complies with Directive 2002/95/EC (RoHS)**

The frequency of this oscillator is stabilized by surface-acoustic-wave (SAW) technology. This results in excellent performance from a compact, rugged, oscillator operating at the fundamental frequency of 1000.0 MHz. The highly-reliable HO4001-1 makes it suitable for general purpose use in a wide variety of applications.

HO4001-1

**1000.0 MHz
SAW
Oscillator**



Dip 16-8 Case

Characteristic	Sym	Notes	Minimum	Typical	Maximum	Units
Operating Frequency	Absolute Frequency	1, 7		1000.0		MHz
	Tune Range		999.850		1000.150	MHz
	Tune Voltage		0		+5	VDC
	Tuning Linearity			3:1	4:1	
RF Output Power	P _O	3, 6	+7	+10		dBm
Discrete Spurious	Second Harmonics	2, 3, 4			-15	dBc
	Third and Higher Harmonics				-20	
	Nonharmonic			-80		
SSB Phase Noise	1 kHz Offset	2, 3, 4		-100	-95	dBc/Hz
	10 kHz Offset			-130	-125	
	100kHz Offset			-150		
RF Impedance	Nominal Impedance	Z _O	3	50		Ω
	Operating Load VSWR	G _L	3, 5		2:1	
DC Power Supply	Operating Voltage	V _{CC}	3, 6	4.75	5.0	VDC
	Operating Current	I _{CC}			45	mA
Operating Ambient Temperature		T _A	3, 6	-20	+70	°C
Lid Symbolization (YY=Year, WW=Week)		RFM HO4001-1 YYWW				



CAUTION: Electrostatic Sensitive Device. Observe precautions for handling.


COCOM CAUTION: Approval by the U.S. Department of Commerce is required prior to export of this device.

Notes:

1. One or more of the following United States patents apply: 4,616,197; 4,610,681; and 4,761,616.
2. Unless noted otherwise, all specifications are listed at T_A = +25°C ±2°C, V_{CC} = nominal voltage ±0.01 VDC, and load impedance = 50 Ω with VSWR ≤ 1.5:1.
3. The design, manufacturing process, and specification of this device are subject to change without notice.
4. Applies to oscillator only and not to sidebands caused by external electrical or mechanical sources. (Dedicated external voltage regulation with low-frequency filtering for the DC power supply and proper circuit board layout are recommended for optimum spectral purity.)
5. For specified maximum operating load VSWR (any angle) at F_O. (No instability or damage will occur for any passive load impedance.)
6. For any combination of V_{CC} and T_A within the specified operating ranges.
7. Applies for any combination of Note 5 and 6 conditions.


DIP16-8

Metal Dual-Inline Package with 8 leads in a 16-lead DIP configuration



Dimension	mm		Inches	
	MIN	MAX	MIN	MAX
A	—	25.02	—	0.985
B	—	12.83	—	0.505
C	—	6.35	—	0.250
D	0.40	0.51	0.016	0.020
E	0.64 Nominal		0.025 Nominal	
F	7.62 Nominal		0.300 Nominal	
G	2.54 Nominal		0.100 Nominal	
H	17.78 Nominal		0.700 Nominal	
K	3.39	6.73	0.130	0.265
L	1.30	—	0.051	—
M	—	11.18	—	0.440
N	—	22.60	—	0.890
R	1.75	2.26	0.069	0.089

BLOCK DIAGRAM



ELECTRICAL CONNECTIONS

