



**2c 15A, 4c 10A polarized  
power relays**

## SP RELAYS



**RoHS compliant**

Protective construction: Dust cover type

### FEATURES

**1. Small, slim form factor**

Facilitating the form factor reduction of devices, the overall height of the relay package is less than half that of our HP relay.

**2. High sensitivity**

The high-efficiency polarized electromagnetic mechanism in conjunction with our exclusive spring alignment method achieves levels of sensitivity higher than relays that have been available up to now. For both the 2 Form C and 4 Form C single side stable and 2 coil latching types, the 150 mW minimum operating power level allows direct driving by transistor or chip controllers.

**3. High reliability and long life**

With a structure that ensures almost perfectly complete twin contact and minimal contact bounce, you get greater reliability than has so far been provided by power relays.

**4. Latching types also available**

1 coil latching and 2 coil latching types are available. In cases where it was formerly unavoidable to use plural relays for large power memory, you can now use a single SP relay.

**5. Strong resistance to vibration and shock**

Our balanced armature technology well withstands vibration and shocks. It provides strong resistance to vibration and shock.

**6. Terminals and mounting boards are available**

### TYPICAL APPLICATIONS

**1. Electrical power device**

**2. Robots**

**3. Railway signal equipment**

**ORDERING INFORMATION**



Contact arrangement  
2: 2 Form C  
4: 4 Form C

Terminal shape  
Nil: Plug-in type  
P: PC board type

Operating function  
Nil: Single side stable  
L: 1 coil latching  
L2: 2 coil latching

Nominal coil voltage  
3, 5, 6, 12, 24, 48 V DC

Notes: 1. PC board type and 1 coil latching type are manufactured by lot upon receipt of order.  
2. Certified by UL, CSA and TÜV

**TYPES**

| Contact arrangement | Nominal coil voltage | Single side stable | 2 coil latching |
|---------------------|----------------------|--------------------|-----------------|
|                     |                      | Part No.           | Part No.        |
| 2 Form C            | 3V DC                | SP2-DC3V           | SP2-L2-DC3V     |
|                     | 5V DC                | SP2-DC5V           | SP2-L2-DC5V     |
|                     | 6V DC                | SP2-DC6V           | SP2-L2-DC6V     |
|                     | 12V DC               | SP2-DC12V          | SP2-L2-DC12V    |
|                     | 24V DC               | SP2-DC24V          | SP2-L2-DC24V    |
|                     | 48V DC               | SP2-DC48V          | SP2-L2-DC48V    |
| 4 Form C            | 3V DC                | SP4-DC3V           | SP4-L2-DC3V     |
|                     | 5V DC                | SP4-DC5V           | SP4-L2-DC5V     |
|                     | 6V DC                | SP4-DC6V           | SP4-L2-DC6V     |
|                     | 12V DC               | SP4-DC12V          | SP4-L2-DC12V    |
|                     | 24V DC               | SP4-DC24V          | SP4-L2-DC24V    |
|                     | 48V DC               | SP4-DC48V          | SP4-L2-DC48V    |

Standard packing (2 Form C): Carton: 20 pcs.; Case: 200 pcs.  
Standard packing (4 Form C): Carton: 10 pcs.; Case: 100 pcs.  
Note: PC board type and 1 coil latching type are manufactured by lot upon receipt of order.  
\* Terminal sockets and mounting boards available.

**RATING**

**1. Coil data**

1) Single side stable

| Nominal coil voltage | Pick-up voltage (at 20°C 68°F)            | Drop-out voltage (at 20°C 68°F)           | Nominal operating current [±10%] (at 20°C 68°F) | Coil resistance [±10%] (at 20°C 68°F) | Nominal operating power | Max. applied voltage     |
|----------------------|---|---|---|---------------------------------------|-------------------------|--------------------------|
| 3V DC                | 70%V or less of nominal voltage (Initial) | 10%V or more of nominal voltage (Initial) | 100mA   | 30Ω                                   | 300mW                   | 150%V of nominal voltage |
| 5V DC                |   |   | 60.2mA  | 83Ω                                   |                         |                          |
| 6V DC                |   |   | 50mA  | 120Ω                                  |                         |                          |
| 12V DC               |   |   | 25mA  | 480Ω                                  |                         |                          |
| 24V DC               |   |   | 12.5mA  | 1,920Ω                                |                         |                          |
| 48V DC               |   |   | 6.2mA   | 7,700Ω                                |                         |                          |

2) 2 coil latching

| Nominal coil voltage | Set voltage (at 20°C 68°F)                | Reset voltage (at 20°C 68°F)              | Nominal operating current [±10%] (at 20°C 68°F) |            | Coil resistance [±10%] (at 20°C 68°F) |            | Nominal operating power |            | Max. applied voltage     |
|----------------------|---|---|---|------------|---------------------------------------|------------|-------------------------|------------|--------------------------|
|                      |   |   | Set coil  | Reset coil | Set coil                              | Reset coil | Set coil                | Reset coil |                          |
| 3V DC                | 70%V or less of nominal voltage (Initial) | 70%V or less of nominal voltage (Initial) | 100mA   | 100mA      | 30Ω                                   | 30Ω        | 300mW                   | 300mW      | 150%V of nominal voltage |
| 5V DC                |   |   | 60.2mA  | 60.2mA     | 83Ω                                   | 83Ω        |                         |            |                          |
| 6V DC                |   |   | 50mA  | 50mA       | 120Ω                                  | 120Ω       |                         |            |                          |
| 12V DC               |   |   | 25mA  | 25mA       | 480Ω                                  | 480Ω       |                         |            |                          |
| 24V DC               |   |   | 12.5mA  | 12.5mA     | 1,920Ω                                | 1,920Ω     |                         |            |                          |
| 48V DC               |   |   | 6.2mA   | 6.2mA      | 7,680Ω                                | 7,680Ω     |                         |            |                          |

## 2. Specifications

| Characteristics            | Item  | Specifications   |  |
|----------------------------|---|--|--|
| Contact                    | Initial contact pressure                                      | 2 Form C: Approx. 0.392 N (40 g 1.41 oz), 4 Form C: Approx. 0.196 N (20 g 0.71 oz)   |  |
|                            | Arrangement   | 2 Form C, 4 Form C   |  |
|                            | Contact resistance (Initial)                                  | Max. 30 mΩ (By voltage drop 6 V DC 1A)   |  |
|                            | Contact material  | Stationary contact: Au flashed AgSnO <sub>2</sub> type, Movable contact: AgSnO <sub>2</sub> type   |  |
| Rating                     | Nominal switching capacity (resistive load)                   | 2 Form C: 15 A 250 V AC, 4 Form C: 10 A 250 V AC   |  |
|                            | Max. switching power (resistive load)                         | 2 Form C: 3,750 VA, 300 W, 4 Form C: 2,500 VA, 300 W   |  |
|                            | Max. switching voltage  | 2 Form C, 4 Form C: 250 V AC, 30 V DC (48V DC: Max. 2A)  |  |
|                            | Max. switching current  | 2 Form C: 15 A (AC) 10 A (DC), 4 Form C: 10 A  |  |
|                            | Nominal operating power                                       | 300mW (Single side stable, 2 coil latching)  |  |
|                            | Min. switching capacity (reference value)*1                   | 100 mA 5V DC   |  |
| Electrical characteristics | Insulation resistance (Initial) (25°C, 50% relative humidity) | Min. 1,000MΩ (at 500V DC)<br>Measurement at same location as "Breakdown voltage" section.  |  |
|                            | Breakdown voltage (Initial)                                   | Between open contacts  | 1,500 Vrms for 1 min. (Detection current: 10 mA)                                       |
|                            |   | Between contact and coil   | 3,000 Vrms for 1 min. (Detection current: 10 mA)                                       |
|                            |   | Between contact sets   | 3,000 Vrms for 1 min. (Detection current: 10 mA)                                       |
|                            | Operate time [Set time] (at 20°C 68°F) (Initial)              | Max. 30 ms [Max. 30 ms]<br>(Nominal coil voltage applied to the coil, excluding contact bounce time.)  |  |
|                            | Release time [Reset time] (at 20°C 68°F) (Initial)            | Max. 20 ms [Max. 30 ms]<br>(Nominal coil voltage applied to the coil, excluding contact bounce time.) (without diode)  |  |
| Mechanical characteristics | Shock resistance  | Functional   | Min. 392 m/s <sup>2</sup> (Half-wave pulse of sine wave: 11 ms; detection time: 10μs.) |
|                            |   | Destructive  | Min. 980 m/s <sup>2</sup> (Half-wave pulse of sine wave: 6 ms.)                        |
|                            | Vibration resistance  | Functional   | 10 to 55 Hz at double amplitude of 3 mm (Detection time: 10μs.)                        |
|                            |   | Destructive  | 10 to 55 Hz at double amplitude of 3 mm  |
| Expected life              | Mechanical  | Min. 5×10 <sup>7</sup> (at 180 times/min.)   |  |
|                            | Electrical (resistive load)                                   | 2 Form C:<br>Min. 10 <sup>5</sup> (15 A 250 V AC [at 20 times/min.]), Min. 10 <sup>5</sup> (10 A 30 V DC [at 20 times/min.])<br>4 Form C:<br>Min. 10 <sup>5</sup> (15 A 250 V AC [at 20 times/min.]), Min. 10 <sup>5</sup> (10 A 30 V DC [at 20 times/min.]) |  |
| Conditions                 | Conditions for operation, transport and storage*2             | Ambient temperature: -50°C to +60°C -58°F to +140°F;<br>Humidity: 5 to 85% R.H. (Not freezing and condensing at low temperature)   |  |
|                            | Max. operating speed  | 20 times/min. (at rated load)  |  |
| Unit weight                |   | 2 Form C: 50 g 1.76 oz; 4 Form C: 65 g 2.29 oz   |  |


Notes: \*1. This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.

\*2. The upper limit of the ambient temperature is the maximum temperature that can satisfy the coil temperature rise value. Refer to Usage, transport and storage conditions in NOTES.

## REFERENCE DATA

### 1.-(1) Coil temperature rise (2 Form C type)


Tested sample: SP2-DC24V



### 1.-(2) Coil temperature rise (4 Form C type)


Tested sample: SP4-DC24V

Ambient temperature: 27 to 29°C 81 to 84°F




2. Electrical life (SP2, 15 A 250 V AC resistive load)

Change of pick-up and drop-out voltage




Change of contact resistance




3. Electrical life (SP4, 10 A 250 V AC resistive load)

Change of pick-up and drop-out voltage



Change of contact resistance




**DIMENSIONS** (mm inch)

The CAD data of the products with a **CAD Data** mark can be downloaded from: <http://industrial.panasonic.com/ac/e/>

**2 Form C**

1) Plug-in terminal


**CAD Data** External dimensions



General tolerance:  $\pm 0.3 \pm 0.12$


2) PC board type

**CAD Data** External dimensions



General tolerance:  $\pm 0.3 \pm 0.12$


PC board pattern (Bottom view)



Tolerance:  $\pm 0.1 \pm 0.04$


Schematic (Bottom view)

Single side stable type



(Deenergized condition)

2 coil latching type




(Reset condition)

Diagram shows the "reset" position when terminals 3 and 4 are energized. Energize terminals 1 and 2 to transfer contacts.

**4 Form C**

1) Plug-in terminal


**CAD Data** External dimensions



General tolerance:  $\pm 0.3 \pm 0.12$


2) PC board type

**CAD Data** External dimensions



General tolerance:  $\pm 0.3 \pm 0.12$


PC board pattern (Bottom view)



Tolerance:  $\pm 0.1 \pm 0.004$


Schematic (Bottom view)

Single side stable type



(Deenergized condition)

2 coil latching type



(Reset condition)

Diagram shows the "reset" position when terminals 3 and 4 are energized. Energize terminals 1 and 2 to transfer contacts.

**SAFETY STANDARDS**

| Item     | UL (Recognized) |                         | CSA (Certified) |                         | TÜV (Certified)      |                                |                 |
|----------|-----------------|-------------------------|-----------------|-------------------------|----------------------|--------------------------------|-----------------|
|          | File No.        | Contact rating          | File No.        | Contact rating          | File No.             | Contact rating                 | Cycles          |
| 2 Form C | E43028          | 15A 250V AC General Use | LR26550         | 15A 250V AC General Use | B 11 08<br>13461 308 | 15A 250V AC ( $\cos\phi=1.0$ ) | 10 <sup>5</sup> |
|          |                 | 1/2HP 125, 250V AC      |                 | 1/2HP 125, 250V AC      |                      | 10A 30V DC (0ms)               | 10 <sup>5</sup> |
|          |                 | 10A 30V DC              |                 | 10A 30V DC              |                      | —                              | —               |
| 4 Form C | E43028          | 10A 250V AC General Use | LR26550         | 10A 250V AC General Use | B 11 08<br>13461 308 | 10A 250V AC ( $\cos\phi=1.0$ ) | 10 <sup>5</sup> |
|          |                 | 1/2HP 125, 250V AC      |                 | 1/2HP 125, 250V AC      |                      | 10A 30V DC (0ms)               | 10 <sup>5</sup> |
|          |                 | 10A 30V DC              |                 | 10A 30V DC              |                      | —                              | —               |

**NOTES**

1. For cautions for use, please read "GENERAL APPLICATION GUIDELINES".

---

Please contact .....

**Panasonic Corporation**

Electromechanical Control Business Division

■ 1006, Oaza Kadoma, Kadoma-shi, Osaka 571-8506, Japan  
[industrial.panasonic.com/ac/e/](http://industrial.panasonic.com/ac/e/)

**Panasonic**<sup>®</sup>

©Panasonic Corporation 2016