


2				1				
LOC	DIST	REVISIONS						
G	14	P	LTR	DESCRIPTION		DATE	DWN	APVD
			K1	REV PER ECR 09-027414		16DEC09	JR	TM



- 1 STAMP AMP 12-10* APPROX AS SHOWN
- 2 WIRE INSULATION DIA: .150-.230
- 3 TONGUE MATERIAL THK: .040±.002
- 4 BODY & SLEEVE: CU PER ASTM B152
BODY & SLEEVE: TIN PLATE .000100 MIN EXT THK PER ASTM B545
INSULATION: NYLON, COLOR - YELLOW
- 5 BODY & SLEEVE: CU PER ASTM B152
BODY: TIN PLATE .000100 MIN EXT THK PER ASTM B545
INSULATION: NYLON PER ASTM D4066
COLOR - YELLOW
- 6 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 7 MEETS MS17143-9, CLASS 1 & 2

OBSOLETE	50	2-327948-1 ON TAPE & REEL	5	2-327948-3
OBSOLETE	500	327948 ON TAPE & REEL	4	2-327948-2
OBSOLETE	2500	LOOSE PIECE	5	2-327948-1
	---	LOOSE PIECE	4	7 327948
QTY		PACKAGE TYPE	MATERIAL FINISH	PART NO

CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 300 VOLT MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] STRANDED OR SOLID
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± -
MATERIAL SEE TABLE	FINISH SEE TABLE

DWN JR RUTH	16DEC09	Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
CHK T MICHIELUTTI	16DEC09			
APVD T MICHIELUTTI	16DEC09	NAME TERMINAL, RECTANGULAR TONGUE, PIDG WIRE SIZE: 12-10 AWG		
PRODUCT SPEC		SIZE	CAGE CODE	DRAWING NO
APPLICATION SPEC		A3	00779	C-327948
WEIGHT	-	RESTRICTED TO		
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV K1