


TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S14A*GV00
15	39.14	33.32	25.18	24.54	19.18	D15S14A*GV00
25	53.03	47.04	39.12	38.25	33.12	D25S14A*GV00
37	69.32	63.50	55.68	54.71	49.68	D37S14A*GV00

Protection: 4 --> flash AU

6 --> 0.76μ AU


LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S14A*GV00LF
15	39.14	33.32	25.18	24.54	19.18	D15S14A*GV00LF
25	53.03	47.04	39.12	38.25	33.12	D25S14A*GV00LF
37	69.32	63.50	55.68	54.71	49.68	D37S14A*GV00LF

Protection: 4 --> flash AU

6 --> 0.76μ AU

PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS: SEE DRAWING C01-8646-0000

European Views

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection mm	size Scale A3 2	
TOLERANCES UNLESS OTHERWISE SPECIFIED			ANGULAR	LINEAR	0.X 0.XX 0.XXX	±0.1 ±0.1 ±0.1	ECN LS06-0097
Dr	PESSON	1992/01/08	Product family		D-SUB		
Eng	PESSON	1992/01/08	D-SUB		Spec ref -		
Chr	LEGARE	1992/01/08	Product family		D-SUB		
Appr	LEGARE	1992/01/08	Product family		D-SUB		
FCI			title		C01-8646-0051		
FEMALE CONNECTOR, LOW PROF			straight solder type for		Rev. F		
catalog no			CUSTOMER		sheet 1 of 1		

rev	ecn no	dr	date
C	-	-	1996/09/04
D	LS05-001	MPE	2005/03/09
E	LS05-0056	MPE	2005/06/27
F	LS06-0097	LGO	2006/07/29
-	-	-	-
-	-	-	-
-	-	-	-