



DESCRIPTION: R/A .590" FEMALE ECONOMY D-SUB



	A	B	C	D
9	1.213 30.81	.984 24.99	.642 16.30	.030 0.76
15	1.541 39.14	1.312 33.32	.971 24.65	.030 0.76
25	2.088 53.04	1.852 47.04	1.512 38.40	.030 0.76
37	2.729 69.32	2.500 63.50	2.157 54.80	.030 0.76



SPECIFICATIONS:

MATERIALS:

SHELL: STEEL, TIN PLATED
INSULATOR: UL 94V-0 RATED BLACK
GLASS-FILLED POLYESTER - UL 94V-0
CONTACTS: BRASS OR PHOSPHOR BRONZE

183-XXX-212-XX1









SERIES _____
NUMBER OF CONTACTS _____
GENDER _____
2 = FEMALE
PC MOUNT _____
TIN SHELL _____
HARDWARE OPTIONS: _____
SEE PAGE 2
PLATING: _____
1 = GOLD FLASH

ELECTRICALS:

CURRENT RATING: 5 AMPS
DIELECTRIC STRENGTH: 1000V AC RMS
INSULATOR RESISTANCE: 1000 MOHMS MIN
TEMPERATURE: -55°C TO +105°C

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS	DATE: 9-24-98
		CHECKED:	DATE:
	SCALE: 1:1		
NorComp		SHEET 1 OF 1	REV 6
		DWG NO. 183-XXX-212-XX1	

DESCRIPTION: R/A HARDWARE OPTIONS

	 METAL SHELL WITH INSIDE GROUND STRAPS	 METAL SHELL	 METAL SHELL FORK BOARD LOCKS	 METAL SHELL FORK BOARD LOCKS
 .120" DIA. HOLE	16	43	N/A	N/A
 4-40 FLUSH INSERT	17	45	57 BOARD LOCKS IN REAR HOLE (.590")	53 BOARD LOCKS IN FRONT HOLE (.590")
 4-40 HEX STANDOFF FEMALE SCREWLOCK	18	48	54 BOARD LOCKS IN REAR HOLE	56 BOARD LOCKS IN FRONT HOLE
 4-40 ROUND STANDOFF FEMALE SCREWLOCK	N/A	N/A	N/A	N/A



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
WAYNE ROBBINS

CHECKED:
PAM JENKINS

SCALE:

DATE:
8-23-98

DATE:
8-24-98

SHEET 1 OF 1

REV 6

NorComp

DWG NO.
183 HARDWARE