




Part Number: 120098-0201

PROFIBUS* 90° D-Sub to 90° D-Sub Connector 5.0m Cable Length



| | |
|------------------|--|
| Status: | OBsolete |
| Replacement: | Contact Molex |
| Series: | 120098 |
| Category: | Industrial Cordsets |
| Overview: | Brad® PROFIBUS Solutions |
| Old Part Number: | @MM3S62PP4M050 |

Series image - Reference only

Product Environmental Compliance

EU RoHS: Compliance Status Not Reviewed
China RoHS:
REACH SVHC: Not Reviewed
Low-Halogen Status: Not Reviewed

Part Detail

General

| | |
|-----------------|--|
| Status | Obsolete |
| Category | Industrial Cordsets |
| Series | 120098 |
| Connector End A | D-Sub (9-pin) |
| Connector End B | D-Sub (9-pin) |
| IP Rating | IP40 |
| NEMA Rating | NEMA 4 |
| Overview | Brad® PROFIBUS Solutions |
| Product Name | Profibus* |
| Type | Double Ended |
| UPC | 78172504507 |

Physical

| | |
|-------------------------------|------------------------|
| Cable Diameter | 8.00mm (.315") |
| Cable Length | 5.0m |
| Color - Cable Jacket | Purple |
| Coupling Style | Threaded |
| Gender | Male-Female |
| Keyway | None |
| LED Indicator | No |
| Material - Cable Jacket | PUR |
| Material - Connector Body | PUR |
| Material - Contact | N/A |
| Material - Coupling Nut | Gray Anodized Aluminum |
| Material - Plating Mating | N/A |
| Orientation | 90° Angle |
| Poles | 9 |
| Temperature Range - Operating | -20°C to +80°C |
| Wire Size AWG | 22 |
| Wire/Cable Type | N/A |

Electrical

(Please review the Product Specification for specific details.)

| | |
|-------------------------------|------------|
| Current - Maximum per Contact | 4A |
| Voltage - Maximum | 250V AC/DC |

Material Info

| | |
|-----------------|----------------|
| Old Part Number | @MM3S62PP4M050 |
|-----------------|----------------|

Reference - Drawing Numbers

Sales Drawing

SD-120098-027

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)