

9097250 TOSHIBA (DISCRETE/OPTO)

56C 07613

D T-33-11

2SC2913

SILICON NPN TRIPLE DIFFUSED TYPE

SWITCHING REGULATOR AND HIGH VOLTAGE
SWITCHING APPLICATIONS.
HIGH SPEED DC-DC CONVERTER APPLICATION.

FEATURES:


- Excellent Switching Times
: $t_r=1.0\mu s$ (Max.), $t_f=1.0\mu s$ (Max.) at $I_C=4A$
- High Collector Breakdown Voltage : $V_{CEO}=400V$

MAXIMUM RATINGS ($T_a=25^\circ C$)

CHARACTERISTIC	SYMBOL	RATING	UNIT
Collector-Base Voltage	V_{CBO}	500	V
Collector-Emitter Voltage	V_{CEO}	400	V
Emitter-Base Voltage	V_{EBO}	7	V
Collector Current	I_C	7	A
Base Current	I_B	2	A
Collector Power Dissipation ($T_c=25^\circ C$)	P_C	40	W
Junction Temperature	T_j	150	$^\circ C$
Storage Temperature Range	T_{stg}	-65 ~ 150	$^\circ C$

INDUSTRIAL APPLICATIONS


Unit in mm

ELECTRICAL CHARACTERISTICS ($T_a=25^\circ C$)

Mounting kit No. AC74

Weight : 7.6g

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Collector Cut-off Current	I_{CBO}	$V_{CB}=400V, I_E=0$	-	-	100	μA
Emitter Cut-off Current	I_{EBO}	$V_{EB}=7V, I_C=0$	-	-	1	mA
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	$I_C=1mA, I_E=0$	500	-	-	V
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C=10mA, I_B=0$	400	-	-	V
DC Current Gain	h_{FE}	$V_{CE}=5V, I_C=3A$	12	-	-	
		$V_{CE}=5V, I_C=7A$	8	-	-	
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C=7A, I_B=1.4A$	-	-	1.0	V
Base-Emitter Saturation Voltage	$V_{BE(sat)}$	$I_C=7A, I_B=1.4A$	-	-	2.0	V
Switching Time	Rise Time	t_r	-	-	1.0	μs
	Storage Time	t_{stg}	-	-	2.5	
	Fall Time	t_f	-	-	1.0	








9097250 TOSHIBA (DISCRETE/OPTO)

56C 07614 D T-33-11

2SC2913

STATIC CHARACTERISTICS



TOSHIBA CORPORATION

9097250 TOSHIBA (DISCRETE/OPTO)

56C 07615 07-33-11

2SC2913