

Display Solutions

Your Value-added Partner for Industrial Display Solutions



[Product Lines](#) > [Display Solutions](#) > [ES-1000 LCD Kits](#) > [ES-1115R-LXAE](#)

Model Information

ES-1115R-LXAE



- [Ordering Information](#)
- [Datasheet \(PDF\)](#)
- [Downloads](#)

15" Color TFT-LCD Kit for LVDS Interface with 4-wire Resistive Touch Screen Kit

Main Features

- LCD Panel: AUO G150XG01
- Display: 1024 x 768 XGA, 262K
- Viewing Angle (L/R/U/D): 60/60/40/60
- Brightness (nit): 350
- Response Time (ms): 16
- Backlight (hrs.): CCFL, 2-tubes, 50,000 hrs
- Operation Temp.: 0 ~ 50 °C
- ES-1115R-LXA-01E ~ 05E LCD Kit Cable Length (mm): 500 (optional)
- Touch Screen Kit: Pre-installed 4-wire Resistive Touch screen kit
- Outline Dimensions mm (W x H x D): 326.5 x 253.3 x 12

Introduction

15" Color TFT-LCD Kit for LVDS Interface with 4-wire Resistive Touch Screen Kit

Ordering Information

Part Number	Description
ES-1115R-LXAE	 15" Color TFT-LCD Kit for LVDS Interface with 4-wire Resistive Touch Screen Kit
ES-1115R-LXA-01E	 15" LCD kit, AUO 280 nites, LVDS-1, XGA, w/TS
ES-1115R-LXA-02E	 15" LCD kit, AUO 280 nites, LVDS-2, XGA, w/TS
ES-1115R-LXA-03E	 15" LCD kit, AUO 280 nites, LVDS-3, XGA, w/TS
ES-1115R-LXA-05E	 15" LCD kit, AUO, LVDS-05, XGA, w/TS
ES-1115R-LXA-04E	 15" LCD kit, AUO 280 nites, LVDS-4, XGA, w/TS

Contact Information

Office	Tel	Email
Advantech Headquarters	886-2-2792-7818	MKT.ACG@advantech.com.tw

Main Menu

- [About Display Solutions](#)
- [CTOS for Display Solutions](#)
- [DTOS Industrial Display Solutions](#)
- [Product News](#)
- [Selection Wizard](#)
- [Virtual Tour](#)
- [Applications](#)
- [Contact Us](#)

Related Links

- [Embedded Computing - x86](#)
- [Embedded Computing - ARMXScale](#)
- [Applied Panel Computers](#)
- [SMART Home Solution](#)

Feature Articles

- [Industrial Computer](#)
- [Panel PC, Flat Panel Computer, Touch Screen, Human Machine Interface](#)