

A

Extruded heatsinks for PCB mounting

for semiconductor screw-mounting

B

C

D

E

F

G

E = mounting method

special lengths and transistor drillings on request

surface treatment: black anodised

H

horizontal for semiconductor screw-mounting




I

K

L

M

N




	 ... STS	 ... STIS	 ... STSB
art. no.	[mm]	R_{th} [K/W]	
SK 104 25,4 ...	25.4	14	TO 220/ SOT 32/ TO 3 P
SK 104 38,1 ...	38.1	11	TO 220/ SOT 32/ TO 3 P
SK 104 50,8 ...	50.8	9	TO 220/ SOT 32/ TO 3 P
SK 104 63,5 ...	63.5	8	TO 220/ SOT 32/ TO 3 P
please indicate:			
... mouting method STS =with solder pin STIS =with solder pins and insulating washer STSB =with threaded bolt M 3, brass			

E = mounting method

special lengths and transistor drillings on request

surface treatment: black anodised

horizontal for semiconductor screw-mounting

			
art. no.	[mm]	R_{th} [K/W]	
SK 104 25,4 LS	25.4	14	TO 220/ SOT 32/ TO 3 P
SK 104 38,1 LS	38.1	11	TO 220/ SOT 32/ TO 3 P
SK 104 50,8 LS	50.8	9	TO 220/ SOT 32/ TO 3 P
SK 104 63,5 LS	63.5	8	TO 220/ SOT 32/ TO 3 P

special lengths and transistor drillings on request

surface treatment: black anodised

A 97

 Heatsinks with threaded rail
 Profiles for PCB components
 Retaining springs for transistors
 Order example

 → A 92
 → A 91
 → A 113 – 118
 → A 21

 Attachable heatsinks for TO-cases
 Mounting for TO 3 angle
 Silicone wafers
 Mica wafers

 → A 93
 → A 122
 → E 2 – 4
 → E 11