






REVISION Q

DO NOT
SCALE FROM
THIS PRINT



SECTION "A"-"A"

FIG 1
HTST-111-01-XX-D-LL SHOWN
* DIMENSIONS APPLY WHEN USING -LL OPTION ONLY

HTST-1XX-XX-XX-D-XX-XX

No OF POSITIONS

-02 (STRAIGHT ONLY)
-03 THRU -18, -20, -24,
-25, -28, -30, -32 & -36

LEAD STYLE

SEE TABLE 1
& TABLE 2

POLARIZATION OPTION

-XX: INDICATES POSITION OMITTED

OPTION

BLANK: STRAIGHT (STYLES -04 & -05 N/A)
-RA: RIGHT ANGLE (STYLES -01, -02 & -03 N/A)
-LL: LOCKING LEAD (STRAIGHT ONLY)
-LA: -RA OPTION WITH -LL OPTION

ROW SPECIFICATION

-D: DOUBLE ROW
(USE HTST-XX-D)


PLATING SPECIFICATION

-G: GOLD, 10 Au / 50 Ni MIN ON CONTACT, 3 Au / 50 Ni MIN ON TAIL
-T: MATTE TIN, CONTACT AND TAIL
-S: SELECTIVE, 30 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
-L: LIGHT SELECTIVE, 10 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
-H: HEAVY GOLD, 30 Au / 50 Ni MIN ON CONTACT, 3Au / 50 Ni MIN ON TAIL
-F: FLASH SELECTIVE, 3 Au / 50 Ni ON CONTACT, MATTE TIN TAIL
-TM: MATTE TIN CONTACT AND TAIL
-SM: SELECTIVE, 30 Au / 50 Ni ON CONTACT, MATTE TIN TAIL
-FM: FLASH SELECTIVE, 3 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
-LM: LIGHT SELECTIVE, 10 Au / 50 Ni MIN, MATTE TIN TAIL

TABLE 1

LEAD STYLE	"A"	TERMINAL
-01	.480 [12.19]	T-1S6-17-XX-2
-02	.530 [13.46]	T-1S6-08-XX-2
-03	.930 [23.62]	T-1S6-11-XX-2

-LL & -LA CRIMP LOCATIONS



EVEN POS

ODD POS

■ = CRIMP LOCATION

DETAIL 'B'

SCALE 6 : 1

NOTES:

1. REPRESENTS A CRITICAL DIMENSION.
2. TERMINAL PUSHOUT FORCE: 3 lbs.
3. ASSEMBLE GOLD PLATED END AS SHOWN.
4. TERMINALS TO BE FLUSH TO .010 [0.25] BELOW TOP OF SHROUD.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS ANGLES
.XX: $\pm .01$ [3] 2°
.XXX: $\pm .005$ [13]
.XXXX: $\pm .0020$ [51]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING

SHEET SCALE: 1.5:1

INSULATOR:
LCP, UL 94 VO
COLOR: NATURAL

TERMINAL: PHOS BRONZE

F:\DWG\MISC\MKTG\HTST-1XX-XX-XX-D-XX-XX-MKT.SLDDRW

DESCRIPTION:




HIGH TEMP TOP SHROUD TERMINAL STRIP

DWG. NO.

HTST-1XX-XX-XX-D-XX-XX

BY: BRATCHER 01/16/04

SHEET 1 OF 2



$.035 \pm .010 [0.89 \pm 0.25]$
(TYP)

$\text{C} \cdot .0080 [0.203]$
(TYP)

TABLE 2					
LEAD STYLE	"B"	"C"	"D"	TERMINAL #1	TERMINAL #2
-04	.130[3.30]	.280[7.11]	.830[21.08]	T-1S6-15-XX-2	T-1S6-10-XX-2
-05	.230[5.84]	.380[9.65]	.930[23.62]	T-1S6-09-XX-2	T-1S6-11-XX-2







FIG 2
-RA & -LA OPTIONS
(HTST-111-04-XX-D-LA SHOWN)
(SAME AS FIG 1, UNLESS OTHERWISE STATED)
* DIMENSIONS APPLY WHEN USING -LA OPTION ONLY



IN-PROCESS 2



**TUBE PACKAGING VIEW FOR
04 & 05 LEAD STYLES**

Packaging Table			
Lead Style	Packaging	TUBES	PLUG
-01	Bulk	N/A	N/A
-02	Bulk	N/A	N/A
-03	Bulk	N/A	N/A
-04	Tube	PT-1-24-12T-109	TP-28
-05	Tube	PT-1-24-12T-109	TP-28

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:

HIGH TEMP TOP SHROUD TERMINAL STRIP

DWG. NO.

HTST-1XX-XX-XX-D-XX-XX

BY: BRATCHER 01/16/04

SHEET 2 OF 2