

SC Class G 600Vac/480Vac, 1/2-60A size-rejecting fuses

RoHS



Catalog symbol:

- SC-(amp)

Description:

Basic protection Class G size-rejecting, current limiting fuses. 1/2 to 6A Fast-acting, 7 to 60A time-delay. Time-delay – 12 seconds (minimum) at 200% of rated current.

Specifications:

Ratings

- Volts
 - 600Vac/170Vdc (1/2-20A)
 - 480Vac/300Vdc (25-60A)
- Amps 1/2-60A
- IR
 - 100kA Vac RMS Sym.
 - 10kA Vdc

Agency information

- UL Listed, Std. 248-5, Class G, Guide JDDZ, File E4273
- CSA Certified, C22.2 No. 248.5, Class 1422-01, File 53787
- CE
- RoHS compliant

EATON

Powering Business Worldwide


Catalog numbers (amps)

SC-1/2	SC-6	SC-30
SC-1	SC-7	SC-35
SC-1-1/2	SC-8	SC-40
SC-2	SC-10	SC-45
SC-2-1/2	SC-12	SC-50
SC-3	SC-15	SC-60
SC-4	SC-20	
SC-5	SC-25	

Carton quantity:

Amp rating	Carton qty.
1/2-20	4
25-60	2

Dimensions - in (mm):



Amp rating	A
1/2-15	1.31 (33.3)
20	1.41 (35.8)
25 to 30	1.62 (41.1)
35 to 60	2.25 (57.1)

Features:


- Meets basic protection requirements of NEC®, CEC®, UL®, and CSA®.
- Most economical overcurrent protection solution compared to circuit breakers.
- For use in various non-demanding, general purpose applications.
- Compact branch-circuit units with high interrupting rating and current-limitation.
- With up to a 600V rating, they can be used in 120/208V, 120/240V, and 277/480V circuits.
- Size rejection by length helps prevent overfusing.
- In general, SC fuses are about 1/2 the size of the 600V NEC® fuse type.
- Fuses 7 amps and above have a degree of overload time-delay that permits them to pass temporary overloads.

Recommended fuse blocks:


Fuse amps	1-Pole	2-Pole	3-Pole
1/2-15	BG30011_	BG30012_	BG30013_
20	BG30021_	BG30022_	BG30023_
25-30	BG30031_	BG30032_	BG30033_
35-60	G30060-1C_	G30060-2C_	G30060-2C_

For additional information on the BG and G Series of Class G fuse blocks, see Data Sheet # 1006.

Time-current curves - average melt:



Current-limitation curves:



The only controlled copy of this data sheet is the electronic read-only version located on the Eaton network drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
Eaton.com

Bussmann Division
114 Old State Road
Ellisville, MO 63021
United States
Eaton.com/bussmannseries

© 2015 Eaton
All Rights Reserved
Printed in USA
Publication No. 1024 — BU-SB13733
August 2015

Eaton and Bussmann are valuable trademarks of Eaton in the US and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton. UL® is a registered trademark of the Underwriters Laboratories, Inc. CSA® and CEC® are a registered trademark of the Canadian Standards Group. NEC® is a registered trademark of the National Fire Protection Association, Inc.