


CHARACTERISTICS												
CATALOG LISTING	ISSUE NUMBER	OPERATING TEMPERATURE	SUPPLY	HOUSING MATERIAL	SENSING RANGE		OUTPUT NOMINAL	MAXIMUM COIL RESISTANCE AT 70°C	NUMBER OF TURNS	PRIMARY CONNECTION	X DIMENSION	SECONDARY CONNECTION
					NOMINAL	MAXIMUM						
CSNS300F-001	I	-40°C TO +85°C	±15V	GLASS FILLED PBT	300A	600A	150mA	34Ω	2000±1	THRU HOLE	330m / 13in	AMP CONNECTOR ON FLYING LEADS
CSNS300F-002	I				150m / 6in	AMP CONNECTOR ON FLYING LEADS						



UNLESS OTHERWISE SPECIFIED TOLERANCES ARE: <table border="1" style="display: inline-table; vertical-align: middle;"> <tr> <td>☐ US (inch) CUSTOMARY</td> <td>☒ SI (mm) METRIC</td> </tr> </table>			☐ US (inch) CUSTOMARY	☒ SI (mm) METRIC	<table border="1"> <tr> <td>DRAWN</td> <td>TMM</td> <td>9OCT02</td> </tr> <tr> <td>CHECK</td> <td>SAV</td> <td>9OCT02</td> </tr> </table>			DRAWN	TMM	9OCT02	CHECK	SAV	9OCT02	Honeywell		
☐ US (inch) CUSTOMARY	☒ SI (mm) METRIC															
DRAWN	TMM	9OCT02														
CHECK	SAV	9OCT02														
NO PLACE X ±.040 ±1 ONE PLACE .X ±.030 ±0,4 TWO PLACE .XX ±.015 ±0,15 THREE PLACE .XXX ±.005 ± ANGLES ± ± ± RAW MATERIAL-COMMERCIAL STANDARD			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.													
THIRD ANGLE PROJECTION 			DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED			TITLE 300A NULL BALANCE, CURRENT SENSOR										
3D PTC ASME Y14.5M-1994			SIZE DWG TYPE DRAWING NAME REV C I MTG-CSN-325 1			SCALE NONE WEIGHT SHEET OF 1										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[CSNS300F-001](#) [CSNS300F-002](#)