H HiTRON

UNIVERSAL AC INPUT HARMONIC CORRECTION AC-DC 19" COMPATIBLE EUROCARD MULTI-OUTPUT 100 WATTS SWITCHING MODE POWER SUPPLIES HPU100 SERIES

FEATURES:

- **ACCOMMODATE UNIVERSAL AC SOURCES**
- **MEET IEC 61000-3-2 HARMONIC CORRECTION**
- **MEET UNIVERSAL SAFETY STANDARDS**
- **19" COMPATIBLE EUROCARD FORMAT**
- **EMI MEET EN 55022 & FCC CLASS B**
- **CE MARKING COMPLIANCE**
- **3U X 10HP X 160MM VMEbus STANDARD**

SPECIFICATION

INPUT SPECIFICATION

Input Voltage: Typ. 90-264Vac with PFC.
Input Connector: DIN 41612 at rear.
Input Frequency: 47-63Hz.
Inrush Current: Typ. <30.6A @ 230Vac.
Input Current: 1.0A @ 115Vac, 0.5A @ 230Vac.
Dielectric Withstand: Meet IEC 60950-1.
EMI: Meet EN 55022 & FCC B.
Power Factor Correction: Meet Harmonic Correction IEC 61000-3-2 .PF typ. 0.97-0.98.
Power Indicator: Green LED.
Power OK Signal: Installed.
Logic Inhibit: Installed.
Hold-up Time: 20mS @ 115Vac & 230Vac.
Earth Leakage: Less than 0.40mA @ 230Vac.

OUTPUT SPECIFICATION

Output Voltage: See Ratings Chart.
Output Current: See Ratings Chart.
Output Connector: DIN 41612 at rear.
Line Regulation: Typ. 0.5%.
Load Regulation: Main VO1 typ. ±1-2.0%.
Aux.VO2 typ. ±2.0% (Mag. Amp.)
Aux.VO3 typ. ±3.0% (PR).
Noise & Ripple: Typ. 1% peak to peak.
OVP: Built-in at main VO1.
Adjustability: Available at VO1 & VO2.
Overload Protection (OLP): Fully protected against output overload and short circuit. Consult the factory for OLP setting.

GENERAL SPECIFICATION

Efficiency: Typ. 73-76%.
Switching Frequency: Fixed frequency 83K Hz.
Circuit Topology: Fixed frequency forward circuit.
Transient Response: Output voltage returns in less than 3mS following a 25% load change.
Safety Standard: IEC 60950-1/UL 60950-1 Class I.
Power Density: 2.0 Watt / Cubic Inch.
Operating Temperature: 0 to +50°C full load. Derates from +50 to +70°C by derating 2%/°C.
Storage Temperature: -25 to +85°C.
Temperature Coefficient: Typ. 0.04% /°C.
Cooling: Forced air flow is recommended for Ta > +50°C full load operation.
Construction format: 10HP(TE) X3UX160mm VMEbus standard Eurocard format.

Note: Due to requests in market and advances in technology, specifications subject to change without notification.

c UL us

TÜV Rheinland BAUART GEPRÜFT TYPE APPROVED

CE

In application

OUTPUT VOLTAGE / CURRENT RATINGS CHART

SINGLE OUTPUT

MODEL NO.	MAIN VO1 ★@#	
	Typ.	**Volt.**
HPU100-S033250	25.0A	**3.3V**
HPU100-S050200 (HPU100-10)	20.0A	**5.0V**
HPU100-S120080	8.0A	**12.0V**
HPU100-S150075	7.5A	**15.0V**
HPU100-S240042 (HPU100-13)	4.2A	**24.0V**
HPU100-S280036	3.6A	**28.0V**
HPU100-S360028	2.8A	**36.0V**
HPU100-S480021	2.1A	**48.0V**

DUAL OUTPUT

MODEL NO.	MAIN VO1 ★@◇		AUX. VO2 @▲◇	
	Typ.	**Volt.**	Typ.	**Volt.**
HPU100-D050I (HPU100-20)	8.0A	**5.0V**	5.0A	**12.0V**
HPU100-D120I (HPU100-21)	4.2A	**12.0V**	4.2A	**12.0V**
HPU100-D050K	8.0A	**5.0V**	4.0A	**15.0V**
HPU100-D150K (HPU100-23)	3.4A	**15.0V**	3.4A	**15.0V**
HPU100-D033I	11.0A	**3.3V**	5.0A	**12.0V**
HPU100-D033K	11.0A	**3.3V**	4.0A	**15.0V**

TRIPLE OUTPUT

MODEL NO.	MAIN VO1 ★@◇		AUX. VO2 @▲◇		AUX. VO3 ●◇	
	Typ.	**Volt.**	Typ.	**Volt.**	Typ.	Volt.
HPU100-T050IE	7.0A	**5.0V**	5.0A	**12.0V**	1.0A	**5.0V**
HPU100-T050KK (HPU100-31)	7.0A	**5.0V**	4.0A	**15.0V**	0.4A	**15.0V**
HPU100-T050II (HPU100-32)	7.0A	**5.0V**	5.0A	**12.0V**	0.5A	**12.0V**
HPU100-T033EI	11.0A	**3.3V**	9.0A	**5.0V**	1.0A	**12.0V**
HPU100-T033KK	10.0A	**3.3V**	4.0A	**15.0V**	0.6A	**15.0V**
HPU100-T033II	10.0A	**3.3V**	5.0A	**12.0V**	0.8A	**12.0V**

Symbol: "★" OVP built-in. "@" Adjustable. "#" Remote sensing. "▲" Magnetic Amplifier.
"◇" Floating (or isolated) output. "●" Installed with Post Regulator.

MECHANICAL DIMENSIONS: MM [INCHES] **WEIGHT:** 920.0g (32.5 Oz.)



INPUT & OUTPUT CONNECTORS PIN ASSIGNMENT

	AC INPUT			SINGLE OUTPUT					DUAL OUTPUT					TRIPLE OUTPUT							Status/ Control	
ASSIGNMENT	**AC-L**	**AC-N**	**AC-G**	**+VO1**	**+S**	**-VO1**	**-S**	**NC**	**+VO1**	**-VO1**	**+VO2**	**-VO2**	**NC**	**+VO1**	**-VO1**	**+VO2**	**-VO2**	**+VO3**	**-VO3**	**NC**	**Log. Inh.**	**P.Ok**
CNTR & Pin#	28	30	32	4,6	8	12,14	10	16,18, 24,26	4	6	8	10	12,14,16 18,24,26	4,6	8,10	12	14	16	18	24,26	20	22

Mating connector: DIN 41612-H15 Female