






Directive 2002/95/EC
"RoHS"
Compliant



NOTES:

1.ELECTRICAL SPECIFICATION:

- 1-1.RATING: 100VAC MAX or 12VDC 2A MAX
- 1-2.INSULATION RESISTANCE: 50MOHM MIN. at 250VDC
- 1-3.WITHSTANDING: 250VAC at 1 MINUTE

2.MATERIAL AND FINISH:

- 2-1.INSULATOR: LCP
- 2-2.PIN: PHOSPHOR BRONZE; PLATING: SELECTIVE GOLD 30u"
- 2-3.SHELL: TIN PLATED STEEL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION DO NOT ALTER CAD DRAWING BY HAND	tolerance unless otherwise specified tolerance shall be as follow			finish		 Dim. in mm	scale:		
	Decimal: $\begin{matrix} .x \\ .xx \\ .xxx \end{matrix}$	Angles:					material:		
				2005	date	name	title: 1.27mm Low Force Helix Connector Solder 60p male type RoHS compliant		
				draw.	Dec. 12	Vincent Ke			
				appd.	Dec. 12	Kathy Skelthorn			
				norm					
				d-old					
							drawing no.:	AutoCAD 2005	DIN A3 sheet 1/1
							16K1A1602		
	rev.	description	date				name		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[33LFHS-60P](#)