




Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTES:

1. SUPPLIED WITH HEX NUT AND INTERNAL TOOTH LOCK WASHER.
2. PARTS WILL BE MARKED M15733/61.

2000	500 VDC / 350 VAC	25 AC	I.R. MIN. @ 100 (VDC.)	DWV	----	55	70	70
	125 °C				10 MHz	100 MHz	1 GHz	10 GHz
MIN. CAP. (pF)	WORKING VOLTAGE	CURRENT (A)	10 G Ω	1250 VDC	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			

X-2015 Rev-0	REVISION RECORD	Original Release C.O. 19990713-1-01	ADDED DWV, IR & DIM. .050. DIM .437 ± .010 WAS .436 ± .046 & .250 ± .010 WAS .250 ± .015. S.M. 11-10-03	20031110-4-01	1	TOLERANCES unless otherwise specified 2 PLC. DECIMAL ± N/A 3 PLC. DECIMAL ± .031 [0.79] ANGLES ± N/A	Title MIL-15733/61-0003 BUSHING STYLE FILTER	
							Drawn S.M. 07-15-99	Scale 2 X
							Approved E.F. 07-15-99	
							TUSONIX TUCSON, ARIZONA	A 4206-502

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4206-502](#)