

Winkelstück für Flex-Lichtleiter Ø2mm und Ø3mm

Technische Daten

Gehäuse-Werkstoff: PC schwarz UL94

Dieses Winkelstück für flexible Lichtleiter-Systeme von Ø2mm und Ø3mm eignet sich hervorragend für die spannungsfreie Konfektionierung aller kundenseitigen Anforderungen. Die Lichtleiter können durch den Kunden exakt und auf engstem Raum genau dort um 90° umgelenkt werden, wo es anforderungsspezifisch notwendig ist. Gerade bei kurzen Lichtleiterlängen und gleichzeitigem Einsatz von mehreren Lichtleitern ist die spannungsfreie Montage auf der Leiterplatte hervorzuheben.




für Lichtleiter Ø for light guides Ø	Art.-Nr.	-
2	1216.0200	-
3	1216.0100	-

Angle Holder for Flex Light Guides Ø2mm and Ø3mm

Technical Data

Housing Material: PC black UL94

This angle holder is especial suitable for customer required fitting of flexible light-guides without any stress for the pc board. This angle for lightguides of Ø2mm and Ø3mm is mounted by customer very easily and exactly by 90° wherever necessary. It doesn't need much space and secures a mounting process without any tension on the pc board, especially by using shorter light guide lengths or several ones like arrays.



Einbaubeispiel · Mounting Example

Adapter für Flex-Lichtleiter 1000µm und 2000µm

Allgemeine Hinweise und Technische Daten

Adapter-Werkstoff: PC schwarz UL94

LL-Werkstoff: PMMA

Linsen-Werkstoff: PC glasklar UL94

Der Adapter dient dazu, das Licht vorhandener Lichtleiter-Elemente mit einem Ø3mm Schaft in liegender sowie in stehender Form an die Frontplatte zu transportieren. Siehe hierzu Seite 10, 11, 16, 18, 19 und 20.



Faser · Fibre	Länge · Length	Art.-Nr.
1000µm	150	1298.1001
2000µm	150	1298.2001

Adapter for Flex Light Guides 1000µm and 2000µm


General Remarks and Technical Data

Adapter-Material: PC black UL94


LL-Material: PMMA

Lens-Material: PC clear UL94

The adapter is designed to transmit the light from lying or upright light guide elements with a Ø3mm shank to the front panel. See pages 10, 11, 16, 18, 19 and 20.



Einbaubeispiel 1298.1001 · Mounting Example 1298.1001



Einbaubeispiel 1298.2001 · Mounting Example 1298.2001