


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

.156 Mating
Snap Diameter



NOTES:
Material : Electro-Tin Plated Copper
Voltage Rating: 600 V
Operating Temp: -40°F to 221°F (-40°C ~ 105°C)

REVISIONS			DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No: 680					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
	A	Redrawn in Autocad	JAP	12/12/91				
1199	B	Redrawn and Renamed	JWM	11/8/01	JC	1/4/02	JC	1/4/02

SPC Part Number	Wire Range (AWG)	L	T	M	Color	Insulating Material
CBP-DY-1415	16 ~ 14	.87	.090	.170	Blue	Nylon 6/6
CBP-DY-1815	18 ~ 22	.85	.070	.145	Red	UL94V-2
CBP-TV-1415	16 ~ 14	.85	.090	.170	Blue	Vinyl (PVC)
CBP-TV-1815	22 ~ 18	.85	.070	.145	Red	UL94V-0

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL. THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



E58918



LR22190M6

OSHA
Acceptable

SPC-F005.DWG

DRAWING TITLE:				SPC TECHNOLOGY			
Insulated Bullet Style Male Disconnects							
DRAWN BY:		DATE:		SIZE		ELECTRONIC FILE	
JC		3/12/91		DWG. NO.		REV	
CHECKED BY:		DATE:		A		TA-439.dwg	
JOHN COLE		12/13/91				TA-439.dwg	
APPROVED BY:		DATE:		SCALE:		SHEET:	
John Liska		12/13/91		NTS		1 OF 1	