

Features

Unregulated Converter

- Industry Standard Pinout
- 1kVDC or 2kVDC Isolation
- UL94V-0 Package Material
- Optional Continuous Short Circuit Protected
- Fully Encapsulated
- Custom Solutions Available
- Efficiency to 85 %

Description

The RE DC/DC converters are typically used in general purpose power isolation and voltage matching applications, and feature a full industrial operating temperature range of -40°C ~ +85°C without derating.

Selection Guide

Part Number SIP 7	(2kV)	Input Voltage (VDC)	Output Voltage (VDC)	Output Current (mA)	Efficiency (%)
RE-xx3.3S	(H)	3.3, 5, 12, 15, 24	3.3	303	75
RE-xx05S	(H)	3.3, 5, 12, 15, 24	5	200	78-80
RE-xx09S	(H)	3.3, 5, 12, 15, 24	9	111	78-80
RE-xx12S	(H)	3.3, 5, 12, 15, 24	12	83	80-84
RE-xx15S	(H)	3.3, 5, 12, 15, 24	15	66	80-84
RE-xx24S	(H)	3.3, 5, 12, 15, 24	24	42	78-85

xx = Input Voltage (other input and output voltage combinations available on request)

* add Suffix "P" for Continuous Short Circuit Protection, e.g. RE-0505S/P, RE-0505S/HP

Specifications (measured at $T_A = 25^\circ\text{C}$, nominal input voltage, full load and after warm-up)

Input Voltage Range	$\pm 10\%$	
Output Voltage Accuracy	$\pm 5\%$	
Line Voltage Regulation	1.2%/1% of V_{in} typ.	
Load Voltage Regulation (10% to 100% full load)	3.3V output type	20% max.
	5V output type	15% max.
	9V, 12V, 15V, 24V output types	10% max.
Output Ripple and Noise (20MHz limited)	100mVp-p max.	
Operating Frequency	50kHz min. / 100kHz typ. / 105kHz max.	
Efficiency at Full Load	70% min. / 80% typ.	
No Load Power Consumption	101mW min. / 126mW typ. / 220mW max.	
Maximum Capacitive Load	33 μ F	
Isolation Voltage	(tested for 1 second)	1000VDC min.
Rated Working Voltage	(long term isolation)	see Application Notes
Isolation Voltage	H-Suffix (tested for 1 second)	2000VDC min.
Rated Working Voltage	H-Suffix (long term isolation)	see Application Notes
Isolation Capacitance	20pF min. / 75pF max.	
Isolation Resistance	10 G Ω min.	
Short Circuit Protection	1 Second	
P-Suffix	Continuous	
Operating Temperature Range (free air convection)	-40°C to +85°C (see Graph)	
Storage Temperature Range	-55°C to +125°C	
Relative Humidity	95% RH	
Package Weight	2.2g	
Packing Quantity	25 pcs per Tube	
MTBF (+25°C)	} Detailed Information see Application Notes chapter "MTBF"	using MIL-HDBK 217F 992 x 10 ³ hours
(+85°C)		using MIL-HDBK 217F 145 x 10 ³ hours

ECONOLINE

DC/DC-Converter

RECOM

1 Watt

SIP7


Single Output



EN-60950-1 Certified

RE


Derating-Graph (Ambient Temperature)




Refer to Application Notes

Typical Characteristics


RE-xx05S



RE-xx12S





RE-xx15S





Package Style and Pinning (mm)

7 PIN SIP Package



Recommended Footprint Details



RE Pin Connections

Pin #	Single
1	+Vin
2	-Vin
4	-Vout
6	+Vout
XX.X ± 0.5 mm	
XX.XX ± 0.25 mm	