


HT

D-Sub connectors - Stamped and Formed Contacts

RIGHT ANGLE HIGH TEMPERATURE AND HIGH DENSITY CONNECTORS



MAIN CHARACTERISTICS

Specifications

- Connectors according to MIL C24308

Materials and platings	
Shells	Steel with nickel plating
Insulator	Glass filled thermoplastic, UL 94V-0
Contacts	Copper alloy, selective gold plating
Rear insert	Brass with nickel plating
Screwlock	Brass with nickel plating
Grounding clip	Copper alloy with tin-lead plating

Electrical Data	
Current rating	3A
Voltage rating	600V AC/rms 50Hz
Withstanding voltage	1000V AC/rms 50Hz for one minute
Insulation resistance	5000MΩ
Contact resistance	10mΩ max

Climatic Data	
Operating temperature	-55°C to + 150° C, resist to short term (30s) at 260°C

Mechanical Data		
Mating and unmating force		
Unit: kg (lb)		
No. of Cts	Mate (max)	Unmate (min)
15	3.81 (8.42)	0.52 (1.14)
26	5.95 (13.16)	1.05 (2.32)
44	9.26 (20.46)	1.37 (3.02)
62	13.48 (29.78)	1.76 (3.88)
Standard plating thicknesses		
<ul style="list-style-type: none"> • gold flash • 0.76 μm (30μ") gold 		

DESCRIPTION

The Amphenol "HT" series allow the customers to use through holes connectors with reflow soldering process.


This series gives you Amphenol's high standards of quality and reliability to meet of your commercial requirements.

*Economical
right angle PCB
high temperature
connectors*

APPLICATIONS


- Industrial
- Telecom
- Any industry standard I / O connections

HT / E14




Amphenol

Shell size dimensions




Nb OF CONTACTS	DIMENSIONS mm (inch)			
	A	B	C	D
15	30.84 (1.214)	24.99 (.984)	16.26 (.640)	2.29 (.090)
26	39.24 (1.545)	33.32 (1.312)	24.56 (.967)	2.29 (.090)
44	53.04 (2.088)	47.04 (1.852)	38.30 (1.508)	2.29 (.090)
62	69.34 (2.730)	63.50 (2.500)	54.76 (2.156)	2.41 (.095)


P.C.B. Layout




15 PIN



62 PIN




26 PIN




44 PIN

Panel mounting option




Front female screwlock
4F/3F



Threaded rear insert
4R/3R

How to order



For special request, please consult factory

Do not hesitate to contact us for further information



Amphenol

Amphenol Socapex
 Telecom Business Unit
 21, chemin du Défois - BP 349
 F - 39100 Dole
 Fax: +33 (0) 3 84 82 94 11
<http://www.dsubconnector.com>
Technical support
 Tel.: +33 (0) 3 84 82 94 00