

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F





E

D


C

B


A



REVISED EC NO: J2011-0208 DRWN: TENAGASE CHKD: CHIKANO APPR: MYAGI	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	MODEL NO. 54366-007	THIRD ANGLE PROJECTION	
		10 UNDER	± 0.2	DRAWN BY	DATE	TITLE USB I/O CONN. (SIDE FLANGE REVERSE SMT TYPE) -LEAD FREE-				
		10 OVER 30 UNDER	± 0.25	CHECKED BY MSASAO	DATE 2004/03/24					
		30 OVER	± 0.3	APPROVED BY		DATE	MOLEX INCORPORATED			
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				



推奨基板寸法
RECOMMENDED PCB LAYOUT



推奨取り付けパネル寸法
RECOMMENDED PANEL LAYOUT

注記
NOTES:

1. 材質
MATERIAL
ハウジング : PA(ポリアミド) 、ガラス充填
白色、UL94V-0
HOUSING : PA (POLYONAMETHYLENE TEREPHTHALAMIDE)
,GLASS FILLED,WHITE,UL94V-0
ターミナル : 燐青銅 (t=0.3)
TERMINAL :PHOSPHOR BRONZE(t=0.3)
シェル : 黄銅 (t=0.4)
SHELL : BRASS(t=0.4)
2. メッキ仕様
PLATING
ターミナル
TERMIAL
接点部 : 金メッキ 最小0.75マイクロメートル
CONTACT AREA:GOLD 0.75 MICROMETER MINIMUM
半田付け部 : 錫メッキ 最小1.0マイクロメートル
SOLDER TAIL AREA:TIN 1.0 MICROMETER MINIMUM
下地メッキ : ニッケルメッキ 最小1.25マイクロメートル
UNDER PLATING:NICKEL 1.25 MICROMETER MINIMUM
シェル : 錫メッキ 最小1.0マイクロメートル
SHELL:TIN 1.0 MICROMETER MINIMUM
下地メッキ : ニッケルメッキ 最小2.0マイクロメートル
UNDER PLATING:NICKEL 2.0 MICROMETER MINIMUM
3. テール平坦度は、最大0.1ミリメートル
TAIL COPLANARITY TO BE 0.1MAXIMUM
4. 本製品は54366-***12の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 54366-***12.

REVISED EC NO: J2011-0208 DRWN: TENAGASE CHKD: CHIKANO APPR: MYAGI A	DESCRIPTION 2010/08/06 2010/08/06 2010/09/03	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	MODEL NO.		54366-***19		
				MM ONLY		---	METRIC	 THIRD ANGLE PROJECTION				
		10 ^{UNDER}		±0.2	DRAWN BY		DATE		TITLE USB I/O CONN. (SIDE FLANGE REVERSE SMT TYPE) -LEAD FREE-			
		10 ^{OVER} 30 ^{UNDER}		±0.25	CHECKED BY		DATE					
		30 ^{OVER}		±0.3	APPROVED BY		DATE		 MOLEX INCORPORATED			
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		54366-0419		SD-54366-007		2 OF 2				
				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

