



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	T2	REVISED PER ECO-16-004223	05AUG2016	NK	MZ



TAPE MTG DETAIL
SCALE 2:1

- 1

0.76µm [.000030] MIN GOLD OVER 1.27µm [.000050] MIN NICKEL.
- 2

2.54µm [.000100] MIN GOLD OVER 1.27µm [.000050] MIN NICKEL.
- 3

WHEN ORDERING CONTACT ASSEMBLY ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:
1. FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL-
A. 1000 PARTS TO A BOX ADD PACKAGING CODE: 1MBOX
2. FOR USE WITH 4/8 INDENT STRIPPER CRIMPER-
A. 1000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL
B. 5000 PARTS TO A REEL ADD PACKAGING CODE: 5MREEL
- 4

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

4 OBSOLETE	SMALL PACK		1	201580-9
	TAPE MTG (SEE DETAIL)		2	201580-7
	TAPE MTG (SEE DETAIL)		1	201580-4
OBSOLETE	STANDARD		2	201580-3
	STANDARD		1	201580-1
	PACKAGING TYPE		SOCKET BODY FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.GELTZ 04/07/93		 TE Connectivity						
DIMENSIONS: mm [INCHES]		CHK R.STONE 4-26-93								
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.S.KLINE 4-29-93		NAME CONTACT ASSEMBLY, SOCKET, #16, 20-24 AWG, TYPE II					
	0 PLC ± -		PRODUCT SPEC							
	1 PLC ± -		—							
	2 PLC ± -		APPLICATION SPEC							
	3 PLC ± -		—							
4 PLC ± -		—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
MATERIAL		FINISH		WEIGHT		A2 00779 C-201580 —				
SOCKET BODY: COPPER ALLOY SPRING: STAINLESS STEEL		SOCKET BODY: SEE TABLE		CUSTOMER DRAWING				SCALE 10:1	SHEET 1 of 1	REV T2