









NOTE:
 PHYSICAL
 1. INNER MOLD WITH PE RESIN 887800008;
 OUTER MOLD WITH BLACK PVC RESIN 887800019.
 ELECTRICAL PERFORMANCE:
 2. DIELECTRIC STRENGTH: 500V DC
 3. INSULATION RESISTANCE: 100M OHMS
 4. CONDUCTIVE RESISTOR: 2 OHMS

887505418	1000+/-20	887808052	S-ATA SIGNAL CABLE, 1.0M RED;
887505318	500+/-10	887808052	S-ATA SIGNAL CABLE, 0.5M RED;
MAT. NO.	LENGTH(MM)	CABLE P/N	DESCRIPTION

B	S-ATA SIGNAL CABLE RED 887808052	SEE TABLE
A	CONNECTOR 675380001	2
ITEM	DESCRIPTION	QTY.

TABLE		QUALITY SYMBOLS		GENERAL TOLERANCES: (UNLESS SPECIFIED)		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION		DIMENSIONS:		SHT		REV	
DESCRIPTION		MAJOR SYMBOLS		mm		INCH		mm		mm		mm		mm		mm	
CRITICAL		=		4 PLACES ±0.		±.		DRAWN BY & DATE		BENTZ 03/01/08		CHECKED BY & DATE		Tony Wong 03/01/08		APPROVED BY & DATE	
1 PLACE ±0.		±.		ANGULAR: ±		°		CAD FILENAME		S88755AD.S001		MATERIAL NO.		SD-88755-004		SHEET NO.	
REV		EC NO.		DRWN: BENTZ 03/01/08		CH'K:		APPR:		A		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		SIZE		A4	




CON1

CON2

SEE TABLE

WIRE CHART



NOTE:
PHYSICAL
1. INNER MOLD WITH PE RESIN 887800008;
OUTER MOLD WITH BLACK PVC RESIN 887800019.
ELECTRICAL PERFORMANCE:
2. DIELECTRONIC STRENGTH: 500V DC
3. INSULATION RESISTANCE: 100M OHMS MIN.
4. CONDUCTIVE RESISTOR: 2 OHMS MAX.

887505418	1000+/-20	40+/-0.8	887808052	S-ATA SIGNAL CABLE, 1.0M RED;
887505318	500+/-10	20+/-0.4	887808052	S-ATA SIGNAL CABLE, 0.5M RED;
MOLEX NO.	LENGTH(MM)	LENGTH(INCH)	CABLE P/N	DESCRIPTION

B	S-ATA SIGNAL CABLE RED 887808052	SEE TABLE	1 PCS
A	CONNECTOR 675380001		2 PCS
ITEM	DESCRIPTION	L	QTY.

TABLE

REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES: (UNLESS SPECIFIED)				SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	DIMENSIONS:			SHT	REVISE ON
			MAJOR	MINOR	ANGULAR	OTHER				MM	INCH	MM		
B	EC NO. DRWN: Louis 04/03/17 CH'K: APPR:		4 PLACES ±0.	3 PLACES ±0.	2 PLACES ±0.	1 PLACE ±0.	DRAWN BY & DATE BENTZ 03/01/08	☒ MM ☐ INCH	☒	MM	INCH	MM ONLY		
A	EC NO. DRWN: BENTZ 03/01/08 CH'K: APPR:		4 PLACES ±0.	3 PLACES ±0.	2 PLACES ±0.	1 PLACE ±0.	CHECKED BY & DATE Tony Wong 03/01/08	☐ MM ☐ INCH	☐	MM	INCH	MM ONLY		
			4 PLACES ±0.	3 PLACES ±0.	2 PLACES ±0.	1 PLACE ±0.	APPROVED BY & DATE Tony Wong 03/01/08	☐ MM ☐ INCH	☐	MM	INCH	MM ONLY		
			4 PLACES ±0.	3 PLACES ±0.	2 PLACES ±0.	1 PLACE ±0.	CAD FILENAME S88755AD.S001	☐ MM ☐ INCH	☐	MM	INCH	MM ONLY		
			4 PLACES ±0.	3 PLACES ±0.	2 PLACES ±0.	1 PLACE ±0.	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.	☐ MM ☐ INCH	☐	MM	INCH	MM ONLY		