

NUMBER 201607

USED ON

NOTES:

⚠️ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE

201607-1

1. AS SHOWN

OBSOLETE

201607-2

1. SAME AS -1 EXCEPT:
2. FINISH OF ITEM 1, .0001 MIN SILVER OVER .00005 MIN NICKEL

⚠️ OBSOLETE

201607-3

1. SAME AS -1 EXCEPT:
2. MT'D ON TAPE.


201607-4

1. SAME AS -1 EXCEPT:
2. FINISH -.000050 GOLD MIN OVER .000050 MIN NICKEL.

201607-5


1. SAME AS -5 EXCEPT:
2. MT'D ON TAPE.

COLOR CODED:
RED



WHEN ORDERING CONTACT ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:

1. FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL—
A. 1000 PARTS TO A BOX ADD PACKAGING CODE: 1MBOX
2. FOR USE WITH 4/8 INDENT STRIPPER CRIMPER—
A. 1000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL
B. 5000 PARTS TO A REEL ADD PACKAGING CODE: 5MREEL



TAPE MT'D ASS'Y
201607-4 AND
201607-6 ONLY.

TOLERANCES
EXCEPT AS NOTED
DECIMALS: ± .005
FRACTIONS: ± 1/64
ANGLES: ± 1/2°

MATERIAL SEE CALL OUT		DR. J. Kaufman 12-1-61	ENGR. B. M. D. 12-5-61
HEAT TREAT H		CHK. J. D. 12-5-61	APP. C. C. 12-5-61
FINISH SEE CALL OUT		AMP INCORPORATED HARRISBURG, PENNA.	
NAME #20 PIN CONTACT ASS'Y			
WIRE SIZE 28-24~.035~.055 INS. DIA			
SCALE 10:1	LOC FT	NO B	REV M1

CUSTOMER DRAWING

PRINT DIST 3 47
DIMENSIONS IN INCHES. DO NOT SCALE PRINT.
PROPOSAL NO

M1	REVISED PER ECO-09-026346	KK	26 NOV 69
M	REACTIVATE -4 PER EC	65	6-9-69
	OGIC-62-98		
L	OBS-3,-4 PER ECN BD5816	RWD	1/92
K	OBS-2 PER ECN BD3038	J. D.	10/69
J	REV PER ECN BD2619	THW	3-8-69
H	REACTIVATE-6/ECN	S. 4770	THW 8-8-69
G	REVISED	S. 4142	THW 9-8-69
F	OBSOLETE -6	J. 724	THW 10-6-69
E	ADDED-6 PER	B. 202	THW 10-6-69
D	NOTE ADDED	B. 141	THW 10-6-69
C	REVISED	B. 119	THW 10-6-69
B	REV. RETAINER SPRING TO SST	Z. 808	THW 10-6-69
A	ADDED-4	J. 361	THW 10-6-69
	REVISED	L. 5	THW 10-6-69
	REVISED	K. 100	THW 10-6-69
	REVISED	S. 341	THW 10-6-69
LTR	REVISION RECORD	ECA	DATE