



Wiremold

6000[®] Series Steel Raceway

Two-Piece Steel Surface Raceway



Wiremold[®] 6000[®] Series Raceway can be used divided for separate wiring circuits or multi-service applications. For large cabling installations, 6000 can be used undivided as headers and feeders or to bring wiring to a specified location. 6000 Series Raceway is ideal for all applications requiring a high cable capacity, dual service steel raceway. Commercial, institutional, and industrial applications all benefit from the 6000 Series rigid steel construction and durable Ivory ScuffCoat[™] finish. 6000 Series Raceway is also ideal for municipalities that require either all steel construction or prohibit nonmetallic cable management systems.





V6000 Raceway shown as a divided system with Activate inserts and power device with a 4050 device bracket.

FEATURES & BENEFITS


- **Steel raceway.** Provides superior strength for any dry interior location installation.
- **Extra large cross sectional area.** Provides space for large wiring requirements or installations that use large diameter cable for power and/or data/communications.
- **Dividable raceway base.** Snap-in divider creates two-compartment raceway. For bringing large amounts of power and data/communications cable to one location.
- **Complete line of fittings.** Provides complete wiring solution and allows for interconnection between raceway systems.
- **Gray baked enamel and Ivory ScuffCoat finish.** Enamel finish assures durability; can be easily overpainted. Durable Ivory Scuffcoat finish makes a scratch resistant surface.
- **Installs as a feeder or header raceway.** Ideal for overhead, open spaces and underfloor applications.
- **Accommodates large size devices.** Large size raceway accepts single- and dual-gang devices up to 100 amps and circuit breakers up to three pole.
- **Pre-cut covers for standard outlet center locations.** For mounting devices on various centers without cutting the covers which reduces number of field cuts for labor savings.
- **Base and cover cutters.** Manually operated cutters are lightweight and portable. Cutters offer labor savings for any size job and maintain a factory clean and square cut.
- **Datacom connectivity options.** Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless and aesthetically pleasing interface for voice, data, audio, and video applications at the point of use.
- **ADA compliant.** Raceway and fittings can be installed in conformance with ADA requirements.
- **UL Listed and CSA Certified.** Raceway UL file E4376 Guide RJBT, CSA file LR350. Fittings UL file 41751 Guide RJPR, CSA file 350 and 48952.

Now compatible with A/V devices.










New 4047 Faceplates accommodate a wide range of power and communications applications.

6000 Series Raceway System Layout



NOTE: Illustration is for showing single service product application only.

















6000 Series Raceway Ordering Information

Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
V6000B G6000B	Base – .060" [1.5mm] galvanized steel. Packed two 10' [3m] lengths per carton. Base has two 9/32" [7.1mm] dia. trade size KOs 1 1/4" [32mm] from each end and on centers of approximately 18" [457mm] throughout. 	660B	 Base Cutter – Portable base cutter. Steel constructed provides clean and easy square cuts. Manual operation required.
V6000C* G6000C*	Cover – .040" [1.0mm] galvanized steel. Packed four 5' [1.5m] per carton. 	660BDK	Replacement Blade Kit – Replacement blade and die set for 640B Cutter.
G6000DA**	Divider – .040" [1.0mm] galvanized steel. One side painted buff primer to provide identification of compartments. Packed four 5' [1.5m] lengths per carton. 	640C	 Cover Cutter – Portable cover cutter. Steel constructed provides clean and easy square cuts. Manual operation required.
		640CDK	Replacement Blade Kit – Replacement blade and die set for 640C Cutter.
		IWE-S GWE-S	 Spray Paint – Used for touching up large areas. Contains 12 oz. of paint. NOTE: Can only be shipped via ground transportation.
		IWE-P GWE-P	 Touch-Up Paint Pen – Used for touching up small areas. Contains 0.3 oz. of paint.

* 4000C and 6000C are compatible with 4000B and 6000B Raceway.

** G6001DA Divider Clips are required to hold divider in place.




6000 Series Raceway Fittings Ordering Information

Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications						
6001A 	Coupling – For joining lengths of 6000B.	V6006 G6006 	Connection Cover – Use where two sections of 4000 or 6000 Cover, not squarely cut, come together.						
G6000WC 	Wire Clip – For holding conductors in place. Use only with undivided 6000 Series Raceway.	V6010B G6010B 	Blank End Fitting – For closing open end of 6000.						
G6001DA† 	Divider Clip – For holding G6000DA Divider in place to divide raceway into 1/3, 1/2, or 2/3 compartments. 6000 Raceway divided into 1/3 compartments will not accept devices.	V6011TX G6011TX 	Combination Flat Elbow – For using as a flat elbow, tee, or cross, (one 6001TX required for tee; two for cross; not included).						
G6001TX 	Converter Coupling – For converting 6011TX or 6017TX into a tee or cross. For tee, one required; for cross, two required.	V6012TX G6012TX 	Internal or External 45° Elbow – For making internal or external 45° turns in a run of 6000. Can also be assembled as an inverted 45° elbow.						
G6008A 	C-Hanger – For suspending 6000 or 4000 Raceway from structural ceiling. Designed for use with 3/8" [9.5mm] rod. Hangers should be installed no more than 5' [1.525m] apart along raceway run. Can be bolted back-to-back for dual runs of 4000, 6000, or to a G3008C for combined runs with 3000 Raceway.	V6014A G6014A 	Connector Fitting – Has 1 1/4", 1 1/2" and 2" [32mm, 38mm and 51mm] trade size KOs in back and on each side.						
V4000C075/ G4000C075* 	Pre-Cut Cover 7.5" [191mm] – For mounting devices on 12" [305mm] centers with 4007, 4046, 4048, and 4049 Series plates.	V6017TX G6017TX 	Combination Internal/External 90° Elbow – For use as internal or external elbow, straight-through fitting, tee, or cross (one G6001TX required for tee or straight through fitting; two for cross; not included).						
V4000C135/ G4000C135 	Pre-Cut Cover 13.5" [345mm] – For mounting devices on 18" [457mm] centers with 4007, 4046, 4048, and 4049 Series plates.	V6046KD G6046KD 	Circuit Breaker Housing – KOs in cover can be removed for installation of three single-pole breakers. For use with the following breakers rated 100A maximum.						
V4000C195/ G4000C195 	Pre-Cut Cover 19.5" [495mm] – For mounting devices on 24" [610mm] centers with 4007, 4046, 4048, and 4049 Series plates.	<table><tr><th>MANUFACTURER</th><th>SERIES</th></tr><tr><td>General Electric</td><td>THQC, THQC</td></tr><tr><td>Westinghouse</td><td>Quicklag, C, QCH</td></tr></table>		MANUFACTURER	SERIES	General Electric	THQC, THQC	Westinghouse	Quicklag, C, QCH
MANUFACTURER	SERIES								
General Electric	THQC, THQC								
Westinghouse	Quicklag, C, QCH								
V4000C315/ G4000C315 	Pre-Cut Cover 31.5" [800mm] – For mounting devices on 36" [915mm] centers with 4007, 4046, 4048, and 4049 Series plates.								



* 4000C and 6000C are compatible with 4000B and 6000B Raceway.

† G6001DA Divider Clips are required to hold divider in place.

6000 Series Raceway Fittings Ordering Information (continued)













Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
V6074 G6074	Take-Off Connector (6000 to 6000) – For 90° tee connection at any point along a run of 6000. 	V6086 G6086	Panel Connector – For connecting 6000 with surface type panel boxes. Accommodates maximum wire capacity of 6000 system. Separate C-flange fits around raceway, covering uneven cuts to the box. Cut 4 3/4" x 3 9/16" [121mm x 90mm] hole in panel box. 
V6074A G6074A	Take-Off Connector (6000 to 4000) – For 90° tee connection at any point along a run of 6000. 		

6000 Series Raceway Faceplates Ordering Information

Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
V6007C-1 G6007C-1	Single-Gang Device Cover – For vertical mounting single-gang devices on undivided raceway. Accepts commercially available wall plate (sold separately). 	V6007C-2 G6007C-2	Two-Gang Device Plate – For installing two-gang devices or two vertically mounted single-gang devices on undivided raceway. Accepts commercially available wall plate (sold separately). 

✦ Add "C" prefix to denote Canadian version – Agency approved for sale in Canada. ®













4047 Series Cover Plates Ordering Information

Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
V4047AX* G4047AX* 	Two-Gang Overlapping Cover Single Round Opening – For straight blade and locking single receptacles with face diameters of 1.38" to 1.39" [35mm to 36mm].	V4047BT* G4047BT* 	Two-Gang Overlapping Cover Duplex & TracJack Mini Adapter – For 15A and 20A duplex receptacles. Includes Mini adapter. Accepts 106 Communications Duplex Frame or two Ortronics® TracJack Communications Inserts.
V4047BX* G4047BX* 	Two-Gang Overlapping Cover Duplex Receptacle – For 15A and 20A duplex receptacles. Accepts 106 Communications Duplex Frame.	V4047C-1* G4047C-1* 	One-Gang Overlapping Device Plate – Use with commercially available two-gang flush plate (sold separately).
V4047BB* G4047BB* 	Two-Gang Overlapping Cover Two Duplex Receptacles – For 15A and 20A duplex receptacles. Accepts 106 Communications Duplex Frame.	V4047C-2* G4047C-2* 	Two-Gang Overlapping Device Plate – Use with commercially available two-gang flush plate (sold separately).
V4047BF* G4047BF* 	Two-Gang Overlapping Cover Duplex & Modular Furniture – For 15A and 20A duplex receptacles. Includes combination Modular Furniture and two Keystone twistouts. Accepts modular furniture adapter, 106 Communications Duplex Frame or RJ45.	V4047JX* G4047JX* 	Two-Gang Overlapping Cover Single Round Opening – For straight blade and single locking receptacles with face diameters of 1.56" – 1.58" [39mm – 40mm].
V4047BM* G4047BM* 	Two-Gang Overlapping Cover Duplex & 2A Mini adapter – For 15A and 20A duplex receptacles. Includes Mini adapter. Accepts 106 Communications Duplex Frame, Activate inserts & Wiremold Open System Communication Modules.	V4047RX* G4047RX* 	Two-Gang Overlapping Cover Rectangle Opening – For rectangular GFCI, Surge and decorator style devices. Does not accept 5507 Series Faceplates.
V4047BS* G4047BS* 	Two-Gang Overlapping Cover Duplex & Series II Mini Adapter – For 15A and 20A duplex receptacles. Includes Mini adapter. Accepts 106 Communications Duplex Frame or one Ortronics® Series II Communications Insert.	V4047RF* G4047RF* 	Two-Gang Overlapping Cover Rectangle Opening & Modular Furniture – For rectangular GFCI, Surge and decorator style devices. Does not accept 5507 Series Faceplates. Accepts modular furniture adapter and RJ45.

NOTE: Faceplates can also be used with 6000 Series Raceway.

* Add "C" prefix to denote Canadian version – UL Listed to U.S. and Canadian Safety Standards. ©

4047 Series Cover Plates Ordering Information (continued)

Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
V4047WX* G4047WX* 	Two-Gang Overlapping Cover with One Duplex Receptacle Installed – Includes one Pass & Seymour Duplex Receptacle with 12" wire leads installed on bracket.	V4047-2BBFF* G4047-2BBFF* 	Four-Gang Overlapping Cover Two Duplex & Two Modular Furniture Openings – For 15A and 20A duplex receptacles. Includes combination Modular Furniture & two Keystone Twistouts. Accepts 106 Communication Duplex Frame, RJ45 or modular furniture adapter.
V4047WF* G4047WF* 	Two-Gang Overlapping Cover with One Duplex Installed & Modular Furniture Opening – Includes one Pass & Seymour 20 A Duplex Receptacle with 12" wire leads installed on bracket. Includes combination Modular Furniture and 2 Keystone Twist Out. Accepts modular furniture adapter and RJ45.	V4047-2BBMM* G4047-2BBMM* 	Four-Gang Overlapping Cover Two Duplex & Two Activate Mini Adapters – For 15A and 20A duplex receptacles. Includes Mini adapter. Accepts 106 Communication Duplex Frame, Activate inserts & Wiremold Open System Communications Modules.
V4047WM* G4047WM* 	Two-Gang Overlapping Cover with One Duplex Installed & Activate Mini adapter – Includes one Pass & Seymour 20A Duplex Receptacle with 12" wire leads installed on Bracket. Includes Mini adapter. Accepts Activate inserts & Wiremold Open System Communication Modules.	V4047-2BBSS* G4047-2BBSS* 	Four-Gang Overlapping Cover Two Duplex & Two Series II Mini Adapters – For 15A and 20A duplex receptacles. Includes Mini adapter. Accepts 106 Communication Duplex Frame or one Ortronics® Series II Communication insert.
V4047WS* G4047WS* 	Two-Gang Overlapping Cover with One Duplex Installed & Series II Mini adapter – Includes one Pass & Seymour 20A Duplex Receptacle with 12" wire leads installed on Bracket. Includes Mini adapter. Accepts one Ortronics® Series II Communications insert.	V4047-2BBTT* G4047-2BBTT* 	Four-Gang Overlapping Cover Two Duplex & Two TracJack Mini Adapters – For 15A and 20A duplex receptacles. Includes Mini adapter. Accepts 106 Communication Duplex Frame or two Ortronics® TracJack Communications inserts.
V4047WT* G4047WT* 	Two-Gang Overlapping Cover with One Duplex Installed & TracJack Mini adapter – Includes one Pass & Seymour 20A Duplex Receptacle with 12" wire leads installed on Bracket. Includes Mini adapter. Accepts two Ortronics® TracJack Communications inserts.	V4047-2BBXX* G4047-2BBXX* 	Four-Gang Overlapping Cover with Two Duplex Openings – For 15A and 20A duplex receptacles. Accepts 106 Communication Duplex Frame.
V4047-2BBBB* G4047-2BBBB* 	Four-Gang Overlapping Cover Four Duplex Openings – For 15A and 20A duplex receptacles. Accepts 106 Communication Duplex Frame.	V4047-2RRXX* G4047-2RRXX* 	Four-Gang Overlapping Cover Two Rectangular Openings – For rectangular, GFCI, Surge and decorator style devices. Does not accept 5507 Series Faceplates.

NOTE: Faceplates can also be used with 6000 Series Raceway.

* Add "C" prefix to denote Canadian version – UL Listed to U.S. and Canadian Safety Standards. ®

4047 Series Cover Plates Ordering Information (continued)

Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
V4047-2WWFF G4047-2WWFF	Four-Gang Overlapping Cover Two Duplex Installed & Two Modular Furniture Openings – Includes two, Pass & Seymour 20A Duplex Receptacles with 12" wire leads installed on Bracket. Includes combination Modular Furniture & four keystone Twistouts. Accepts modular furniture adapter or RJ45.	V4047-2WWTT G4047-2WWTT	Four-Gang Overlapping Cover with Two Duplex Installed & Two TracJack Mini Adapters – Includes two Pass & Seymour 20A Duplex Receptacles with 12" wire leads installed on Bracket. Includes Mini adapter. Accepts four Ortronics® TracJack Communications inserts.
V4047-2WWMM G4047-2WWMM	Four-Gang Overlapping Cover with Two Duplex Installed & Two Activate Mini Adapters – Includes two Pass & Seymour 20A Duplex Receptacle with 12" wire leads installed on Bracket. Includes Mini adapter. Accepts two Activate inserts & Wiremold Open System Communication Modules.	V4047-2WWXX G4047-2WWXX	Four-Gang Overlapping Cover with Two Duplex Receptacles Installed – Includes two Pass & Seymour 20A Duplex Receptacles with 12" wire leads installed on Bracket.
V4047-2WWSS G4047-2WWSS	Four-Gang Overlapping Cover with Two Duplex Installed & Two Series II Mini Adapters – Includes two Pass & Seymour 20A Duplex Receptacles with 12" wire leads installed on Bracket. Includes Mini adapter. Accepts two Ortronics® Series II Communication inserts	V4047UX G4047UX	Bump-Up Extron® MAAP Device Plate – Accepts four Extron® Electronics MAAP single space modules.
		V4047VX G4047VX	Bump-Up Extron® AAP Device Plate – Accepts two Extron® Electronics AAP single space modules.

NOTE: Faceplates can also be used with 6000 Series Raceway.
 * Add "C" prefix to denote Canadian version – UL Listed to U.S. and Canadian Safety Standards. (UL)

4047 Series Configurable Cover Plates Number Logic

1. For "X", Choose one of the following options:


V Ivory & UL Listed
G Gray & UL Listed

CV Ivory & cULus Listed (Canada only)
CG Gray & cULus Listed (Canada only)

2. Choose a Plate Configuration:


Two-Gang Plate:

X 4047 Y Y
 1 2



Four-Gang Plate:

X 4047-2 Y Y Y Y
 1 2 3 4



3. For "Y", Choose any combination of configurations from the options listed below:

- A. 1.41" [35.8mm] Diameter, Single Round Receptacle
- B. Duplex Receptacle Opening
- F. Combination Modular Furniture & 2 Keystone Twist Out
- H. Mouse Hole Twist Out & Grommet

- J. 1.59" [40mm] Diameter, Single Round Receptacle
- M. Pass & Seymour Activate 2A Mini adapter Opening with Adapter
- R. Rectangular Receptacle
- S. Ortronics Series II 2A Mini adapter Opening with Adapter




- T. Ortronics TracJack 2A Mini Adapter Adapter Opening with Adapter
- W. Pass & Seymour Light Almond 20 Amp Receptacle pre-pigtailed with 12" wire leads installed on Bracket
- X. Blank
- Z. 3 Keystone Twist Out

4. Finished Part Number





_ 4047 _ _ _ 4047-2 _ _ _ _

NOTE: For additional colors or configurations, call 1-800-621-0049, option 2.
















4000 Series Faceplates Ordering Information

Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
V4046H-2 G4046H-2 	Tap-Off Fitting – Has four concentric 1/2" and 3/4" trade size KOs.	V6007C-2 G6007C-2 	Two-Gang Device Plate – For installing two-gang devices or two vertically mounted single-gang devices on undivided raceway. <ul style="list-style-type: none"> • Accepts commercially available wall plate (not furnished).
V6007C-1 G6007C-1 	Single-Gang Device Cover – For vertical mounting single-gang devices on undivided raceway. Accepts commercially available wall plate (sold separately).	NOTE: Faceplates can also be used with 6000 Series Raceway. * Add "C" prefix to denote Canadian version – UL Listed to U.S. and Canadian Safety Standards. (UL)	

Communication Endplates Ordering Information

Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
ARA-S2 	Angled Raceway Adapter – For use with multi-channel raceway device brackets and WallSource device mounting brackets. Angled exit provides additional mounting depth required for A/V connections as well as ensuring the required bend radius for UTP and fiber optic cabling. Holds two Ortronics® Series II modules. Fits 5507 Series Faceplate opening.	CM-EPLA* 	End Plates – Includes two outlet identification labels with clear covers and two matching screw covers. Required for mounting Pass & Seymour Activate and Wiremold Open System communication modules into 4050 Series device brackets.
CM-ARA 	Angled Raceway Adapter – For use with multi-channel raceway device brackets and WallSource device mounting brackets. Angled exit provides additional mounting depth required for A/V connections as well as ensuring the required bend radius for UTP and fiber optic cabling. Holds two CM2 Series modules or two Pass & Seymour® 2A inserts. Fits 5507 Series Faceplate opening.	S2-EPL* 	End Plates – Includes two outlet identification labels with clear covers and two matching screw covers. Required for mounting Ortronics Series II modules into 4050 Series device brackets.

V/G4050 & 5507 Series Faceplates Ordering Information

Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
V4050* G4050* 	Device Mounting Bracket – High impact plastic mounting bracket and trim plate which overlap raceway cover providing a seamless transition. For use with 5507 Series Faceplates, Ortronics® TracJack & Series II Modules, Pass & Seymour Activate Series Inserts, and Wiremold Open System Communication Modules.	5507RJ* 	Dual RJ11/RJ45 Connector Faceplate – For mounting one or two RJ type keystone connectors – has one opening and a KO for the other.
5507AD* 	Modular Furniture Adapter – For mounting Pass & Seymour Activate modular furniture adapter and other modular furniture adapters.	5507FRJ* 	Flush Dual RJ11/RJ45 Faceplate – Same as 5507RJ except the connectors are recessed to provide a flush installation.
5507B* 	Blank Faceplate – For covering unused compartments in the device bracket.	5507AAP 	Extron® AAP Faceplate – Accepts two Extron® Electronics AAP single space modules. NEW!
5507D* 	Duplex Faceplate – For covering duplex style devices. Accepts 106 Communication Duplex Frame.	5507MAAP 	Extron® MAAP Faceplate – Accepts two Extron® Electronics MAAP single space modules. NEW!
5507R* 	Rectangular Faceplate – For covering rectangular style devices.	5507-4TJ* 	Ortronics Faceplate – For mounting Ortronics® communication inserts. Accepts four TracJack Devices.
5507S* 	Rectangular Spacer – For mounting commercial device plates. Installs between the device bracket and a device.	5507-6TJ* 	Ortronics Faceplate – For mounting Ortronics® communication inserts. Accepts six TracJack Devices.
5507SW* 	Switch Faceplate – For covering standard toggle switches.		
5507T1* 	Single Receptacle Faceplate – For covering single receptacles – 1.59" [40.4mm] diameter.		
5507T2* 	Single Receptacle Faceplate – For covering single receptacles – 1.41" [35.8mm] diameter.		

NOTE: All faceplates are 4 1/4" long x 1 11/16" wide [108mm x 43mm].

* Add "G" suffix to indicate gray finish.

Not for use with 4048BF and 4048RF Device Covers.

6000 Series Raceway Wire Fill Capacity Charts

6000 Raceway Wire Fill Capacity for Power

WIRE SIZE THHN/THWN	O.D. inches [mm]	NUMBER OF CONDUCTORS (40% FILL)							
		WITHOUT DEVICES		WITH DUPLEX RECT. DEVICES 1.59 in. ² [1025mm ²]		WITH SURGE/ GFCI DEVICES 2.30 in. ² [1485mm ²]		LARGE SINGLE RECEPTACLES 3.00 in. ² [1935mm ²]	
		UNDIV.	DIVIDED	UNDIV.	DIVIDED	UNDIV.	DIVIDED	UNDIV.	DIVIDED
14 AWG	0.111 [2.8]	659	296	528	231	470	202	412	173
12 AWG	0.130 [3.3]	481	216	385	168	342	147	300	126
10 AWG	0.164 [4.2]	303	136	243	106	216	92	189	79
8 AWG	0.216 [5.5]	174	78	140	61	124	53	109	45
6 AWG	0.254 [6.5]	126	56	101	44	89	38	78	33
4 AWG	0.324 [8.2]	77	34	0	0	0	0	0	0
3 AWG	0.352 [8.9]	65	29	0	0	0	0	0	0
2 AWG	0.384 [9.8]	55	24	0	0	0	0	0	0
1 AWG	0.446 [11.3]	40	18	0	0	0	0	0	0
1/0 AWG	0.486 [12.3]	34	15	0	0	0	0	0	0
2/0 AWG	0.532 [13.5]	28	12	0	0	0	0	0	0

NOTE: For additional information, refer to the Technical Section of ED1560 (Product Guide).

6000 Raceway Cable Fill Capacities for Data/Communications

CABLE TYPE	CATEGORY / DESIGNATION	O.D.		DIVIDED		UNDIVIDED	
		Inches	[mm]	20% FILL	40% FILL	20% FILL	40% FILL
UNSHIELDED TWISTED PAIR	4-pair, 24 AWG Cat 3	0.190	[4.8]	50	101	112	225
	4-pair, 24 AWG Cat 5e	0.210	[5.3]	41	83	92	184
	4-pair, 24 AWG Cat 6	0.250	[6.3]	29	58	65	130
TELEPHONE	2-pair, 24 AWG	0.140	[3.6]	93	187	207	415
	3-pair, 24 AWG	0.150	[3.8]	81	163	181	362
	4-pair, 24 AWG	0.190	[4.8]	50	101	112	225
	25-pair, 24 AWG	0.410	[10.4]	10	21	24	48
COAXIAL	RG58/U	0.195	[5.0]	48	96	107	214
	RG59/U	0.242	[6.1]	31	62	69	139
	RG62/U	0.242	[6.1]	31	62	69	139
	RG6/U	0.270	[6.9]	25	50	55	111
TWINAXIAL	100 Ohm	0.330	[8.4]	16	33	37	74
SHIELDED TWISTED PAIR	TYPE 1	0.390	[9.9]	12	24	26	53
	TYPE 2	0.465	[11.8]	8	16	18	37
	TYPE 3	0.245	[6.2]	30	61	67	135
FIBER	Mini ZipCord	0.079 x 0.157	[2 x 4]	116	232	258	516
	ZipCord	0.118 x 0.236	[3 x 6]	51	103	115	230
	Round 4 Strand Fiber	0.187	[4.8]	52	104	115	233
	Round 6 Strand Fiber	0.256	[6.5]	27	55	62	124

NOTE: Capacity range is calculated at 20% to 40% of raceway area as stated in a proposed revision to the Commercial Building Standard for Telecommunication Pathways & Spaces, TIA/EIA-569. Actual wire fill capacity may vary based on applications, cable types, and number, as well as type of fittings. (Fitting may cause additional variances to the fill capacity.)

DATACOM CONNECTIVITY OPTIONS

Now you have a wide range of options for providing datacom connectivity into Wiremold/Legrand Pathways. They are:

- **Ortronics® TracJack® and Series II Modular Connectivity Solutions**
- **Pass & Seymour Activate™ Modular Inserts**
- **Open System Communication Modules**

Ortronics® Connectivity

TracJack® Individual Jack System

- Front-loading, snap-in design supports future moves adds and changes
- Inserts for voice, data, audio, and video
- Available Category 3, 5e, 6, USOC 6-position, and other media
- Flat or angled 45° exit configurations
- Choice of 13 colors and color matched to Wiremold Systems
- Universal T568A/B wiring format



Series II Front-Loading, Module System

- Module design features easy snap-in front-loading design
- Linear 110 punch down format for easy termination
- Inserts for voice, data, audio, and video
- Available Category 3, 5e, 6, USOC 6-position, and other media
- Available in flat or angled 45° exit configurations
- Color matched to Wiremold Systems




For detailed product selection refer to the Ortronics Catalog or visit www.ortronics.com.

Pass & Seymour Legrand Network Wiring

Activate™ Series Front-Loading Inserts

- Modular inserts for voice, data, audio and video applications
- Front-load, snap-in design
- Color and texture matched to Wiremold Systems
- Available Category 3, 5e, 6, as well as 6-position USOC
- Universal T568A/B wiring format




For detailed product selection refer to the Pass & Seymour Network Wiring Catalog or visit www.passandseymour.com.

Open Connectivity Solutions

Wiremold Open System Communications Modules

- Accommodate a wide range of manufacturers' communications outlets including keystone jacks, as well as proprietary solutions from Avaya (Systimax) and NORDX
- Modules insert into a wide range of Wiremold Systems
- Pre-punched faceplates accept common communication devices



NOTE: For more information on integrating connectivity into Wiremold Cable Management Systems contact the Wiremold Applications Engineering Team or your local Wiremold Sales Representative.



Wiremold

WIREMOLD

U.S. and International:

60 Woodlawn Street • West Hartford, CT 06110
1-800-621-0049 • FAX 860-232-2062 • Outside U.S. 860-233-6251

Canada:

570 Applewood Crescent • Vaughan, Ontario L4K 4B4
1-800-723-5175 • FAX 905-738-9721

ED530R14 - Updated May 2010 - For latest specs visit www.legrand.us/wiremold



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Wiremold:

[G6010B](#) [G6000B-10](#) [G6000C](#) [G6000DA](#) [V6000B-10](#)