






THIS DRAWING IS UNPUBLISHED. DIFFUSION RESTREINTE	RELEASED FOR PUBLICATION LIBRE A LA DIFFUSION	20
(C) COPYRIGHT BY ALL RIGHTS RESERVED. TOUS DROITS RESERVES		

FILA ADMISSIBLES (ACCEPTABLES WIRES)	
JAUGE (AWG) SECTION / 7 BRINS (7 STRANDS)	28-26 0.08-0.12mm ²
ISOLANT: Ø MAX / MATIERE (INSUL.: Ø MAX / MAT'L)	Ø 1 / PVC

LOC	DIST	REVISIONS					
F	7	P	LTR	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
			C1	REVISED PER ECO-11-005150	28APR11	RK	HMR



46.52	43.18	18	1-281786-8	*
38.90	35.56	15	1-281786-5	*
31.28	27.94	12	1-281786-2	*
26.20	22.86	10	1-281786-0	*
21.12	17.78	8	0-281786-8	*
16.04	12.70	6	0-281786-6	*
13.50	10.16	5	0-281786-5	*
10.96	7.62	4	0-281786-4	*
8.42	5.08	3	0-281786-3	*
5.88	2.54	2	0-281786-2	
C	A, B	Nb DE POS	REFERENCES (PART No)	
DIMENSIONS				

1	CES CONNECTEURS SONT PREVUS POUR ETRE ACCOUPLES AVEC LES EMBASES 'HE1402' SIMPLE RANGEE	(THESE CONNECTORS ARE DESIGNED TO BE MATED WITH 'HE1402' HEADERS SINGLE ROW)
2	LES REFERENCES SUIVIES D'UN ' * ' SONT LES VERSIONS NORMALISEES SELON LA 'CEI 603-8'	(THE PART-No FOLLOWED BY ' * ' ARE COVERED BY THE INTERNATIONAL STANDARD 'IEC603-8')
	REVETEMENT DES CONTACTS: ETAME	(CONTACTS PLATING: TIN)
	8.6 SIGNIFIE JAUGE 28-26	8.6 REFERS TO 28-26 AWG
	MATIERES - BOITIER: PBT UL94V0, BLEU - CONTACTS: BRONZE PHOSPHOREUX.	(MATERIAL - HOUSING: PBT UL94V0, COLOR BLUE - CONTACTS: PHOSPHOR BRONZE)