







SECTION B-B




		20	47.5	52.4		-	-	-	3-1534797-0
		19	45	49.9		-	-	-	5-1534797-9
		19	45	49.9		-	-	-	4-1534797-9
		19	45	49.9		-	-	-	3-1534797-9
		16	37.5	42.4		-	-	-	3-1534797-6
		15	35	39.9		-	-	-	3-1534797-5
		14	32.5	37.4		-	-	-	3-1534797-4
		13	30	34.9		-	-	-	3-1534797-3
		12	27.5	32.4		-	-	X	4-1534797-2
		12	27.5	32.4		-	-	-	3-1534797-2
		11	25	29.9		10/11		X	5-1534797-1
		11	25	29.9		9/10	-	-	4-1534797-1
		11	25	29.9		-	-	-	3-1534797-1
		10	22.5	27.4		X		-	6-1534796-0
		10	22.5	27.4			-	-	3-1534796-0
		10	22.5	27.4		7/8	-	-	7-1534796-0
		9	20	24.9		-	-	-	3-1534796-9
		8	17.5	22.4		3/4	-	-	6-1534796-8
		8	17.5	22.4		-	X	-	5-1534796-8
		8	17.5	22.4		-	-	-	3-1534796-8
		7	15	19.9	2/3	-	-	-	7-1534796-7
		7	15	19.9		X	-	-	6-1534796-7
		7	15	19.9		X	-	-	5-1534796-7
Blue		7	15	19.9		-	-	-	3-1534796-7
		6	12.5	17.4		2/3	-	-	6-1534796-6
		6	12.5	17.4	4/5	-	-	-	2-1534796-6
		6	12.5	17.4		X	-	-	5-1534796-6
		6	12.5	17.4		-	-	X	4-1534796-6
Brown		6	12.5	17.4		-	-	-	3-1534796-6
		5	10	14.9		1/2	-	-	4-1534796-5
Black		5	10	14.9	2/3	-	-	-	6-1534796-5
Black		5	10	14.9		-	-	-	3-1534796-5
		4	7.5	12.4	2/3	-	-	-	8-1534796-4
		4	7.5	12.4	3/4	-	-	-	5-1534796-4
		4	7.5	12.4	1/2	-	-	-	6-1534796-4
		4	7.5	12.4		X	-	-	7-1534796-4
RED		4	7.5	12.4		-	-	X	4-1534796-4
		4	7.5	12.4		-	-	-	3-1534796-4
Red		3	5	9.9	2/3	-	-	-	2-1534796-3
		3	5	9.9		-	-	X	8-1534796-3
		3	5	9.9		2/3	-	-	9-1534796-3
		3	5	9.9		X	-	-	6-1534796-3
		3	5	9.9		X	-	-	7-1534796-3
		3	5	9.9		-	-	-	3-1534796-3
		2	2.5	7.4		-	-	-	1534796-2
Color Code	CAVITY LOADED	POS. Polzahl	DIM A	DIM B					PN Bestell-Nr.

2	SEE TABLE	CONTACT/Kontakt	CuSn	TINNED/verzinkt
	siehe Tabelle	HOUSING/Federleistengenh.	PA 6 GF UL94-V2	NATUR/Natur
SL NO	PN Bestell-Nr.	DESCRIPTION Beschreibung	MATERIAL	COLOUR/FINISH Farbe/Oberfläche

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. Karabyik 24/04/2002 CIR B. Schnaubelt 24/04/2002 T. Klenner 24/04/2002		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME AMP DUOPUG 2.5 MARK II FEMALE CONNECTOR 2-20 POSITION	
		0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±0.1°		PRODUCT SPEC 108-16785 APPLICATION SPEC 114-18467	
MATERIAL -		FINISH -		SIZE A1	
		WEIGHT -		CAGE CODE 00779	
		CUSTOMER Drawing		DRAWING NO C=1534796	
				RESTRICTED TO 10-1 SHEET 1 of 2 REV 17	

PCB LAYOUT KEYED / CONNECTED ONLY WITH ADDITIONAL FRAME
Leiterplattenanschluss kodiert / nur in Verbindung mit zusätzlichem Rahmen



PCB LAYOUT FOR KEYING BETWEEN POSITION

