



Sensing and Control

[\(U\)](#)

Honeywell.com (<http://www.honeywell.com>)
Test & Measurement
(<https://measurementsensors.honeywell.com/>)

Search the entire website and product database

[HOME](#)
(/sensinghome)

[ABOUT US](#) (/about
honeywell sensing and
control)

[KEY INDUSTRIES
SERVED](#) (/industries)

[PRODUCTS & INFORMATION](#)
(/products & information)

[Start Here ...](#)
[NEWS & EVENTS](#) (/index.php?
ci_id=2533&la_id=1)

[Search](#)
[SALES & SUPPORT](#)
(/index.php?ci_id=2596&la_id=1)

[LOGIN](#)
(/login)

600-128-CBL

([Home](#) (/index.php?ci_id=3972&la_id=1) : [Products](#) (/products) : [Sensors](#) : [Rotary Position Sensors](#) : [Encoders](#) : 600)



600 Series optical encoder, 128 pulse per revolution, 2-square wave, 190,5 mm [7.5 in] cable, mounting hardware included

Actual product
appearance may vary.

Distributor Inventory

Input part number for stock availability

Narrow Your Search**Modify Your Search****Products**

Select Option

Technology

Select Option

Industries Served

Select Option

[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#)

[Specs](#)

[Documentation](#)

[Application Notes](#)

Product Specifications

Encoder Type	Optical
Pulse Per Revolution	128 pulses/revolution
Dome Switch	No
Output	2-square wave, Channel A leads Channel B by 90 ° electrically in counterclockwise direction
Electrical Travel	Continuous
Source Voltage Range	4.75 Vdc min., 5.0 Vdc nom., 5.25 V max.
Supply Current	30 mA
Output Voltage	2.4 Vdc min. (out high); 0.4 Vdc max. (out low)
Pull-up Resistor	10 kOhms
Operating Speed	300 RPM max.
Operating Torque	0,011 N m [1.5 oz in] max.
Terminal	190,5 mm [7.5 in] long cable/lead
Terminal Strength	0,9 kg [2.0 lb]
Housing Type	Molded thermoplastic
Mechanical Travel	Continuous
Rotational Life	10 million shaft rotations
Shaft Axial Force	6,8 kg [15 lb] push/pull
Shaft Radial Play	0,254 mm [0.01 in] at 25,4 mm [1 in]
Shaft Material	Stainless steel
Bushing Material	Nickel-plated brass
Operating Temperature	-40 °C to 65 °C [-40 °F to 149 °F]
Storage Temperature	-55 °C to 110 °C [-67 °F to 230 °F]
Humidity	85 %RH at 40 °C [104 °F] 240 hr
Series Name	600
Availability	Global
UNSPSC Code	30211929
UNSPSC Commodity	30211929 Encoders

Product Search

Product Type: ☐ New Products OnlyIndustry: ☒ Entire Product CatalogSearch Term: **Search**

My Links

eCOM Login (/index.php?ci_id=50629&la_id=1)
Request Access to eCOM (/ecom access request)
Rep/AD Portal Login (/index.php?ci_id=50606&la_id=1)
Rep/AD Portal Access Request (/index.php?ci_id=50630&la_id=1)
Sample Request (/samplerequest)
Digital University Login (/index.php?ci_id=50607&la_id=1)
Limitless Microsite (/index.php?ci_id=50631&la_id=1)
Supplier Microsite (/index.php?ci_id=44887&la_id=1)

Literature and Media

Data Sheets (/white paper and technical data sheets library)
Videos (/videos)
Literature (/literature)
Literature Request (/index.php?ci_id=50636&la_id=1)
White Papers (/whitepapers)
Application Notes (/application notes)
Application Demos (/index.php?ci_id=141383&la_id=1)
CAD Renderings (/cad renderings)

Contacts

Customer Service (/index.php?ci_id=50608&la_id=1)
Technical Support (/index.php?ci_id=50609&la_id=1)
Global Sales & Service (/index.php?ci_id=50610&la_id=1)
Website Feedback (/index.php?ci_id=142628&la_id=1)

[Terms & Conditions \(/index.php?ci_id=2588&la_id=1\)](#)[Privacy Statement \(/index.php?ci_id=2589&la_id=1\)](#)[Site Map \(/sitemap\)](#)