


PRODUCT NUMBER
73327-XXXLF

PLATING OPTION		PACKAGE OPTION	
1 =	GXT 0.76 μ m	1 =	TAPE ON REEL
3 =	GOLD 0.76 μ m	2 =	TUBE
5 =	GOLD 1.27 μ m	3 =	TAPE ON REEL IN PLASTIC BAG


1 = FULLY LOADED
TERMINAL LOADING

WHEN NEEDED, SUFFIX LETTER "LF" INDICATES THE PRODUCT IS ROHS COMPATIBLE, SEE NOTE 4.



NOTES:

- 1 – MATERIAL: HOUSING: HIGH TEMP. NYLON, COLOUR BLACK.
TERMINAL: PHOSPHOR BRONZE.
- 2 – PLATING: CONTACT AREA: SEE TABLE.
SOLDER TAIL : 90/10 SnPb 2µm MIN.
WHEN SUFFIX “LF” IS REQUIRED 2µm MIN MATTE
TIN OVER 1.27 MIN NI IS SUPPLIED INSTEAD OF SnPb
NO RAW EDGES EXEPT SOLDER TAIL TIPS
- 3 – SOLDER TAILS COPLANARITY : 0.1 mm
- 4 – RoHS COMPATIBLE PRODUCT SPECIFICATIONS
- o – PLATING:
 - “LF” MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.
- b – MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO
245°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.
- c – LABELLING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
- d – LEGAL STATEMENT: SEE GS-22-008
- 5 – PACKAGING FOR OPTION 3 : EACH REEL IS WRAPPED INTO A PL
TO PROTECT FROM MOISTURE DURING STACKING TIME.




CUSTOMER COPY FOR REFERENCE ONLY

[illegible]





FCIconnect.com

Copyright FCI



CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface ISO 1302		✓	tolerance ISO 406 ISO 1101		projection 		product family MOD JACK										
ltr	ecn no		dr	date		tolerances unless otherwise specified						title SMT RA JACK 4 POS NARROW INSIDE									
A	F04-0363		DLE	04.10.18		angles				±0.13											
B	F06-0240		DLE	06.07.18		linear				mm 		scale 2:1									
						±2°															
						dr	D LEGRAND		04.10.18		dwg no 73327										
						engr	P NIZZI		04.10.18												
						chr	D LEGRAND		04.10.18		sheet 3 of - A4										
						appd	P NZ		04.10.18												
sheet index		revision sheet									type CUSTOMER Drawing										