

4

3

2

1

D

D

C







C

B

B

A

A



NOTES:

1. Unless otherwise noted, all dimensions are in inches.
2. Break all sharp edges, de-burr & remove loose chips.
3. Material: Aluminum (M/F AAVID Thermalloy 5684 stamping blank)
4. Machine 1.25×1.25 area of surface -A- flat to within $.002$ in/in.
5. Finish: Anodize per MIL-A-8625, Type II, Class 2, Black
Typical breakdown voltage $> 300V$
6. Mark with contrasting ink as shown, if specified by P.O.
7. Approximate Weight: 1.9 oz [$54g$]

TOLERANCES - UNLESS OTHERWISE SPECIFIED

.XX = $\pm .05$ [.002]
.XXX = $\pm .005$ [.0002]
ANG. = $\pm 2^\circ$



TITLE:

HEATSINK, TO-3

SUBJECT:

MECHANICAL DRAWING

ENGINEER:

D-M P.ECK

DCA:

12434

SPL:

1

OF

1

MODEL:

HS02

FILENAME:

HS02

REV:

K

DATE:

14NOV12

4

3

2

1