



LOC		DIST		REVISIONS			
F	LTR	DESCRIPTION		DATE	DWN	APVD	
B		REV: EC 0B40-0259-01		23OCT01	TLP	CD	
C		ECO-06-016706		13JUL2006	JM	BM	




- 1 MATERIAL: JACK HOUSING - POLYPHENYLENE OXIDE, 94V-0 RATED.
TERMINAL BLOCK - POLYPHENYLENE OXIDE, 94V-0 RATED.
STUFFER CAP - POLYCARBONATE, CLEAR, 94V-0 RATED.
DOOR - POLYCARBONATE, CLEAR, 94V-0 RATED.
JACK CONTACTS - PHOSPHOROUS BRONZE, PLATED WITH
1.27um [0.00050] MINIMUM THICK GOLD IN LOCALIZED
AREA AND 3.81um [0.00150] MINIMUM THICK MATTE TIN IN
SOLDER AREA OVER 1.27um [0.00050] MINIMUM THICK
NICKEL UNDERPLATE.
- 2 TOOLLESS WILL TERMINATE 22-24 AWG SOLID CONDUCTORS AND 24 AWG
STRANDED CONDUCTORS, 1.14 [0.045] MAXIMUM INSULATION DIAMETER.
- 3 CAVITY CONFORMS TO FCC RULES AND REGULATIONS)
PART 68 SUBPART F REQUIREMENTS.
- 4 MOUNTING PANEL THICKNESS 1.473 - 1.600 [0.058 - .063].
- 5 THESE TWO SUGGESTED CUTOUT OPENINGS ARE USED
IN TANDEM WITH DUAL FRONT AND BACK CUTOUTS.
- 6 ONE MODULAR JACK ASSEMBLY PER POLYBAG.
- 7 ASSEMBLY SHIPPED WITH STUFFER CAP NOT LATCHED
AT REAR OF HOUSING ASSEMBLY AS SHOWN.
- 8 DIMENSION SHOWN WITH STUFFER CAP IN LATCHED POSITION.



OPEN POSITION



SEE DETAIL A



DETAIL A
SCALE 10:1


PART NUMBER

COLOR CODE	IDC TERMINAL	MODULAR JACK	
WHITE/BLUE			5
BLUE			4
WHITE/ORANGE			3
ORANGE			6
WHITE/GREEN			1
GREEN			2
WHITE/BROWN			7
BROWN			8


ELECTRICAL SCHEMATIC
T568A

COLOR CODE	IDC TERMINAL	MODULAR JACK	
WHITE/BLUE			5
BLUE			4
WHITE/ORANGE			1
ORANGE			2
WHITE/GREEN			3
GREEN			6
WHITE/BROWN			7
BROWN			8

ELECTRICAL SCHEMATIC
T568B



SINGLE PANEL CUTOUT



SUGGESTED FLUSH MOUNT
PANEL APPLICATION CUTOUT

PACKAGE	HOUSING COLOR	PART NUMBER
	ELECTRIC IVORY	1-1339189-1
	VIOLET	1-1339189-0
	GREEN	1339189-9
	YELLOW	1339189-8
	RED	1339189-7
	BLUE	1339189-6
	ORANGE	1339189-5
	NEMA GRAY	1339189-4
	WHITE	1339189-3
	BLACK	1339189-2
	LIGHT ALMOND	1339189-1

TYCO ELECTRONICS CORPORATION 11115 DOWNSIDE DRIVE, HARRISBURG, PA 17105-3608 SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN P. PEPE 09JUN99	tyco Electronics AMP Incorporated Harrisburg, PA 17105-3608 OBSELETE NOT THE LATEST REVISION
DIMENSIONS: mm [INCHES]		CHK P. PEPE 09JUN99	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD P. PEPE 09JUN99	
9 PLC ±.01 1 PLC ±.01 2 PLC ±.01 3 PLC ±.01 4 PLC ±.01 ANGLES ±.01		PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING	
MATERIAL FINISH		SIZE CASE CODE DRAWING NO. 00779 C=1339189	RESTRICTED TO SHEET 4 OF 1