



Search Results

- Evaluate
 - [FAQ's](#)
- How to Buy
 - [Bill of Material](#)
 - [Favorite Products List](#)
 - [Locate Distributor](#)

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#)

Text Search: 'HSTTV38-C'

Your search criteria matched only one product, shown below

HSTTV38-C



Flexible Polyolefin VW-1 DRY-SHRINK™ Heat Shrink Tubing on Small Reels

- For dry locations
- Highly flame retardant
- Fast Shrink Time
- Material Type: Highly Flexible Crosslinked Polyolefin
- Shrink Ratio: 2:1
- Temperature Range: -67°F to 257°F (-55°C to 125°C)
- Voltage: 600V
- UL VW-1 Recognized, CSA Certified
- Mil Spec: AMSDTL-23053/5 Class 3

Part Number	HSTTV38-C
RoHS Compliancy Status	Compliant
Part Description	Thin Wall Polyolefin Heat Shrink (UL224 VW1)
Material	Polyolefin cross-linked
Color	Black
CSA Certified	Yes
Military Specification	AMS-DTL-23053/5 Class 3
UL Recognized	E122770
Length (m)	30.5
CE Compliant	No
CE Marking	No
Flammability Rating	UL224 VW-1
Length Per Reel (ft.)	100
Length Per Reel (m)	30.5
Max. Recovered I.D. (In.)	.187
Max. Recovered I.D. (mm)	4.8
Min. Expanded I.D. (In.)	.375
Min. Expanded I.D. (mm)	9.5
Nominal Diameter (In.)	.375
Nominal Diameter (mm)	9.5
Nominal Recovered Wall Thickness (In.)	.025
Nominal Recovered Wall Thickness (mm)	0.6
Pricing Description	Heat Shrink Thin VW1, .38"(9.5mm) Dia, Black
Shrink Ratio	2:1
Temperature Range	-67°F to 257°F (-55°C to 125°C)
Min. Order UOM	RL
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.