


Semi-Precision Mil-Qualified Metal Glaze™ Resistor

RL Series

- MIL-R-22684
- ± 200 ppm/°C
- 1/4 watt to 1/2 watt
- 2% and 5% tolerance
- 4.3 ohms to 470K ohms



 All Pb-free parts comply with EU Directive 2011/65/EU (RoHS2)

Electrical Data

MIL Type	Marking	Tolerance (±%)	T.C. (ppm/°C)	Power Rating (watts)	Resistance Range (ohms)*	Nominal Size	Max Voltage Rating
RL07	Band	2, 5	200	1/4 @ 70°C	51 to 150K	1/4W	250
RL20	Band	2, 5	200	1/2 @ 70°C	4.3 to 470K	1/2W	350

* For values below or above Mil Resistance, the **Non-Mil** part can be used. But keep in mind -- it is a non-mil part.

Environmental Data


Test Conditions	MIL-R-22684 Test Limits Allowed	RL07 Max. %ΔR (±3σ)
Temperature Coefficient (ppm/°C)	±200	±200
Low Temperature Operation	±0.50%	±0.10%
Thermal Shock	±1.00%	±0.15%
Moisture Resistance	±1.5%	±0.05%
Short Time Overload	±0.50%	±0.10%
Load Life (70°C --- 1/4W) 1000 hours	±2.00%	±0.40%
Terminal Strength	±0.50%	±0.10%
Effect of Soldering	±0.50%	±0.10%
Shock	±0.50%	±0.05%
Vibration	±0.50%	±0.05%
High Temperature Exposure (150°C No Load)	N/A	±0.75%
Rated Power for 10,000 hours at 70°C	N/A	±0.60%
Temperature Rise @ 1/4W Power Load	-	See Temperature Rise Chart
Dielectric Strength	±0.50%	±0.05%

General Note


TT Electronics reserves the right to make changes in product specification without notice or liability.
 All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

RL Series

Physical Data

					
Dimensions (Inches and (mm))					
Nominal Size	Body Length BL	Body Diameter BD	Lead Length LL	Lead Diameter LD	Clean Lead
1/4 watt	0.250 ±0.015 (6.4 ±0.4)	0.090 ±0.008 (2.3 ±0.2)	1.50 ±0.125 (38.1 ±3.2)	0.025 ±0.002 (0.64 ±0.05)	0.310 (7.9)
1/2 watt	0.390 ±0.010 (9.9 ±0.3)	0.140 ±0.008 (3.6 ±0.2)	1.50 ±0.125 (38.1 ±3.2)	0.032 ±0.002 (0.81 ±0.05)	0.450 (11.4)

Commercial Power Derating Chart




General Note

TT Electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

RL Series

MIL Spec. Power Derating Chart



Ordering Data

Sample Part No.	RL	07	S	1001	G
MIL Style					
RL = Fixed Film Resistor					
Power Rating					
07 = 1/4 watt					
20 = 1/2 watt					
Lead Material					
S = Solderable/weldable leads					
Resistance					
First three digits represent significant figures;					
fourth digit is number of zeros.					
Tolerance					
G = 2%, J = 5%					

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT Electronics' own data and is considered accurate at time of going to print.