

Tru Bond 18200 Series

Plastic Bonding Adhesives

ORDERING INFORMATION

	<table> <tr> <th><u>Stock No.</u></th><th><u>Package Size</u></th></tr> <tr> <td>18201</td><td>1 Litre</td></tr> <tr> <td>18206</td><td>1 Litre</td></tr> <tr> <td>18210</td><td>25ml</td></tr> </table>	<u>Stock No.</u>	<u>Package Size</u>	18201	1 Litre	18206	1 Litre	18210	25ml
<u>Stock No.</u>	<u>Package Size</u>								
18201	1 Litre								
18206	1 Litre								
18210	25ml								
Description	A tough UV/Visible light cure-based product that creates permanent bonds to many plastics. Adhesive cures in seconds to ABS, Polycarbonate and Acrylic. It creates a flexible resilient polymer with outstanding impact resistance and flex. Product is able to cure through most translucent substrates.								
Features	• One component UV adhesive • Fast Curing • Available in 3 different viscosities								

PRODUCT DATA

Typical Physical Properties Uncured	<table> <tr> <td>Colour</td><td>Clear</td></tr> <tr> <td>Viscosity cps</td><td></td></tr> <tr> <td>18201</td><td>810</td></tr> <tr> <td>18206</td><td>1,700</td></tr> <tr> <td>18210</td><td>850,000</td></tr> <tr> <td>Non Volatile materials</td><td>99%</td></tr> <tr> <td>Flashpoint</td><td>> 38°C</td></tr> <tr> <td>Specific Gravity g/ml</td><td>1.15</td></tr> <tr> <td>Solubility</td><td>Alcohols, Ketones, oxygenated solvents</td></tr> </table>	Colour	Clear	Viscosity cps		18201	810	18206	1,700	18210	850,000	Non Volatile materials	99%	Flashpoint	> 38°C	Specific Gravity g/ml	1.15	Solubility	Alcohols, Ketones, oxygenated solvents
Colour	Clear																		
Viscosity cps																			
18201	810																		
18206	1,700																		
18210	850,000																		
Non Volatile materials	99%																		
Flashpoint	> 38°C																		
Specific Gravity g/ml	1.15																		
Solubility	Alcohols, Ketones, oxygenated solvents																		
Typical Physical Properties Cured	<table> <tr> <td>Tensile Strength</td><td>9.6 MPa</td></tr> <tr> <td>Elongation</td><td>450%</td></tr> <tr> <td>Volume Shrinkage</td><td>4.7%</td></tr> <tr> <td>Water absorption (ASTM D570) 24 Hrs</td><td>2.4 %</td></tr> <tr> <td>Shore Hardness</td><td>61D</td></tr> <tr> <td>Temperature Range</td><td>-54°C – 107°C</td></tr> <tr> <td>Adhesive Lap Shear (Acrylic)</td><td>3.3 MPa</td></tr> <tr> <td>Adhesive Lap Shear (PETG)</td><td>3.9 MPa</td></tr> <tr> <td>Adhesive Lap Shear (Polycarbonate)</td><td>6.7 MPa</td></tr> </table>	Tensile Strength	9.6 MPa	Elongation	450%	Volume Shrinkage	4.7%	Water absorption (ASTM D570) 24 Hrs	2.4 %	Shore Hardness	61D	Temperature Range	-54°C – 107°C	Adhesive Lap Shear (Acrylic)	3.3 MPa	Adhesive Lap Shear (PETG)	3.9 MPa	Adhesive Lap Shear (Polycarbonate)	6.7 MPa
Tensile Strength	9.6 MPa																		
Elongation	450%																		
Volume Shrinkage	4.7%																		
Water absorption (ASTM D570) 24 Hrs	2.4 %																		
Shore Hardness	61D																		
Temperature Range	-54°C – 107°C																		
Adhesive Lap Shear (Acrylic)	3.3 MPa																		
Adhesive Lap Shear (PETG)	3.9 MPa																		
Adhesive Lap Shear (Polycarbonate)	6.7 MPa																		

Fixture Time and Tack-free time	Light Source	Irradiance	Fixture Time/Sec	Tack-free Time/Sec
	CT100	20 mW/cm ²	<2	N/A
	Fusion® D Bulb	1,000 mW/cm ²	<1	<2
	Synchron Inc. Model 400	250 mW/cm ²	<1	10

Depth of cure (mm, min)	Light Source	Irradiance	Exposure Time
	400 W Metal Halide Bulb	20 mW/cm ²	30 Seconds 1 mm

Unit 3, Shipton Way, Express Business Park, Northampton Road, Rushden, NN10 6GL, UK

ITW Devcon Industrial Products GmbH, Liebigstraße 21, 24145 KIEL, Deutschland/Germany



Tru Bond 18200 Series

Plastic Bonding Adhesives

APPLICATION INFORMATION

Processing	ITW Devcon products are easily applied by syringe dispense or specialty valve spray units. That materials cure extremely fast in bond lines, e.g. where the surfaces are not exposed to air, with UV or visible radiation. Exposure doses range from 0.5 – 2 mJ/cm ² depending on the intensity of the lamps and configuration of the assembly.
Storage and shelf life	Store away from light between 12° and 32°C Shelf life is 12 months from date of manufacture
Precaution	For complete safety and handling information, please refer to Material Safety Data Sheets prior to using this product.
Warranty	Devcon will replace any material found to be defective. Because the storage, handling and application of this material is beyond our control we can accept no liability for the results obtained.
Disclaimer	All information on this data sheet is based on laboratory testing and is not intended for design purposes. ITW Devcon makes no representations or warranties of any kind concerning this data. For product information visit www.devconeurope.com alternatively for technical assistance please call +44 (0) 870 458 7388 or +49 431 718830 (Germany)