



Surface Mount ESD Protection Diodes



MARKING (example only)



Bar = cathode marking

YY = type code (see table below)

XX = date code

FEATURES

- For surface mounted applications
- Low-profile package
- Optimized for LAN protection applications
- Ideal for ESD protection of data lines in accordance with IEC 61000-4-2 (IEC 801-2)
- Ideal for EFT protection of data lines in accordance with IEC 61000-4-4 (IEC 801-4)
- ESD-protection acc. IEC 61000-4-2
± 30 kV contact discharge
± 30 kV air discharge
- Low incremental surge resistance, excellent clamping capability
- 200 W peak pulse power capability with a 10/1000 μ s waveform, repetition rate (duty cycle): 0.01 %
- “Low-Noise” technology - very fast response time
- High temperature soldering guaranteed: 260 °C/10 s at terminals
- e3 - Sn
- AEC-Q101 qualified
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912

AUTOMOTIVE
GRADE
Available



RoHS
COMPLIANT
HALOGEN
FREE
Available

ORDERING INFORMATION

PART NUMBER (EXAMPLE)	ENVIRONMENTAL AND QUALITY CODE				PACKAGING CODE		ORDERING CODE (EXAMPLE)
	AEC-Q101 QUALIFIED	RoHS-COMPLIANT + LEAD (Pb)-FREE TERMINATIONS		TIN PLATED	3K PER 7" REEL (8 mm TAPE), 30K/BOX = MOQ	10K PER 13" REEL (8 mm TAPE), 50K/BOX = MOQ	
		STANDARD	HALOGEN-FREE				
SMF5V0A-		E		3	-08		SMF5V0A-E3-08
SMF5V0A-			M	3	-08		SMF5V0A-M3-08
SMF5V0A-	H	E		3	-08		SMF5V0A-HE3-08
SMF5V0A-	H		M	3	-08		SMF5V0A-HM3-08
SMF5V0A-		E		3		-18	SMF5V0A-E3-18
SMF5V0A-			M	3		-18	SMF5V0A-M3-18
SMF5V0A-	H	E		3		-18	SMF5V0A-HE3-18
SMF5V0A-	H		M	3		-18	SMF5V0A-HM3-18

PACKAGE DATA

PACKAGE NAME	MOLDING COMPOUND	WEIGHT (mg)	HEIGHT MAX. (mm)	LENGTH MAX. (mm)	WIDTH MAX. (mm)	MOLDING COMPOUND	MOISTURE SENSITIVITY LEVEL	SOLDERING CONDITIONS
SMF (DO-219AB)	Standard	15	1.08	3.9	1.9	UL 94 V-0	MSL level 1 (according J-STD-020)	260 °C/10 s at terminals
	Halogen-free							

**ABSOLUTE MAXIMUM RATINGS** ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

PARAMETER	TEST CONDITIONS	SYMBOL	VALUE	UNIT
Peak pulse current	$t_p = 10/1000\text{ }\mu\text{s}$ waveform	I_{PPM}	see "Electrical Characteristics"	A
Peak pulse power	$t_p = 8/20\text{ }\mu\text{s}$ waveform acc. IEC 61000-4-5	P_{PP}	1000	W
	$t_p = 10/1000\text{ }\mu\text{s}$ waveform		200	W
Peak forward surge current	8.3 ms single half sine-wave	I_{FSM}	50	A
ESD immunity	Contact discharge acc. IEC 61000-4-2; 10 pulses	V_{ESD}	± 30	kV
	Air discharge acc. IEC 61000-4-2; 10 pulses		± 30	kV
Thermal resistance	Mounted on epoxy glass PCB with 3 mm x 3 mm, Cu pads ($\geq 40\text{ }\mu\text{m}$ thick)	R_{thJA}	180	K/W
Forward clamping voltage	$I_F = 50\text{ A}$, $t_p = 400\text{ }\mu\text{s}$	V_F	2.5	V
Operating temperature	Junction temperature	T_J	- 55 to + 150	$^{\circ}\text{C}$
Storage temperature		T_{STG}	- 55 to + 150	$^{\circ}\text{C}$

ELECTRICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

PART NUMBER	TYPE CODE		REVERSE BREAKDOWN VOLTAGE at I_T , $t_p = 5\text{ ms}$	TEST CURRENT	REVERSE WORKING VOLTAGE	REVERSE CURRENT at V_{RWM}	PEAK PULSE CURRENT $t_p = 10/1000\text{ }\mu\text{s}$	REVERSE CLAMPING VOLTAGE at I_{PPM}	CAPACITANCE at $V_R = 0\text{ V}$, $f = 1\text{ MHz}$	PROTECTION PATHS
	STD.	HALOGEN-FREE	$V_{BR}\text{ MIN. (V)}$	$I_T\text{ (mA)}$	$V_{RWM}\text{ (V)}$	$I_R\text{ (}\mu\text{A)}$	$I_{PPM}\text{ (A)}$	$V_C\text{ MAX. (V)}$	$C_D\text{ TYP. (pF)}$	$N_{channel}$
SMF5V0A	AE	NE	6.40	10	5	5	21.7	9.2	1120	1
SMF6V0A	AG	NG	6.67	10	6	26	19.4	10.3	1063	1
SMF6V5A	AK	NK	7.22	10	6.5	20	17.9	11.2	938	1
SMF7V0A	AM	NM	7.78	10	7	3	16.7	12	843	1
SMF7V5A	AP	NP	8.33	1	7.5	0.1	15.5	12.9	773	1
SMF8V0A	AR	NR	8.89	1	8	0.1	14.7	13.6	706	1
SMF8V5A	AT	NT	9.44	1	8.5	0.1	13.9	14.4	674	1
SMF9V0A	AV	NV	10	1	9	0.1	13.5	15.4	640	1
SMF10A	AX	NX	11.1	1	10	0.1	11.8	17	562	1
SMF11A	AZ	NZ	12.2	1	11	0.1	11	18.2	509	1
SMF12A	BE	OE	13.3	1	12	0.1	10.1	19.9	483	1
SMF13A	BG	OG	14.4	1	13	0.1	9.3	21.5	423	1
SMF14A	BK	OK	15.6	1	14	0.1	8.6	23.2	392	1
SMF15A	BM	OM	16.7	1	15	0.1	8.2	24.4	367	1
SMF16A	BP	OP	17.8	1	16	0.1	7.7	26	343	1
SMF17A	BR	OR	18.9	1	17	0.1	7.2	27.6	324	1
SMF18A	BT	OT	20	1	18	0.1	6.8	29.2	320	1
SMF20A	BV	OV	22.2	1	20	0.1	6.2	32.4	283	1
SMF22A	BX	OX	24.4	1	22	0.1	5.6	35.5	271	1
SMF24A	BZ	OZ	26.7	1	24	0.1	5.1	38.9	244	1
SMF26A	CE	PE	28.9	1	26	0.1	4.8	42.1	230	1
SMF28A	CG	PG	31.1	1	28	0.1	4.4	45.4	227	1
SMF30A	CK	PK	33.3	1	30	0.1	4.1	48.4	207	1
SMF33A	CM	PM	36.7	1	33	0.1	3.8	53.3	198	1
SMF36A	CP	PP	40	1	36	0.1	3.4	58.1	178	1
SMF40A	CR	PR	44.4	1	40	0.1	3.1	64.5	172	1
SMF43A	CT	PT	47.8	1	43	0.1	2.9	69.4	165	1
SMF45A	CV	PV	50	1	45	0.1	2.8	72.7	162	1
SMF48A	CX	PX	53.3	1	48	0.1	2.6	77.4	161	1
SMF51A	CZ	PZ	56.7	1	51	0.1	2.4	82.4	151	1
SMF54A	CA	PA	60	1	54	0.1	2.25	88	148	1
SMF58A	CC	PC	64.4	1	58	0.1	2.1	95	144	1



TYPICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

Fig. 1 - ESD Discharge Current Wave Form acc. IEC 61000-4-2 (330 Ω /150pF)


Fig. 4 - Pulse Waveform












Fig. 2 - 8/20 μs Peak Pulse Current Wave Form acc. IEC 61000-4-5

Fig. 5 - Typical Capacitance C_D vs. Reverse Voltage V_R



Fig. 3 - Peak Pulse Power Rating


Fig. 6 - Typical Capacitance C_D vs. Reverse Voltage V_R



Fig. 7 - Typical Capacitance C_D vs. Reverse Voltage V_R

Fig. 10 - Typical Reverse Voltage V_R vs. Reverse Current I_R

Fig. 8 - Typical Capacitance C_D vs. Reverse Voltage V_R

Fig. 11 - Typical Reverse Voltage V_R vs. Reverse Current I_R

Fig. 9 - Typical Reverse Voltage V_R vs. Reverse Current I_R

Fig. 12 - Typical Reverse Voltage V_R vs. Reverse Current I_R




PACKAGE DIMENSIONS in millimeters (inches): **SMF**



Foot print recommendation:



Created - Date: 15. February 2005
Rev. 3 - Date: 13. March 2007
Document no.:S8-V-3915.01-001 (4)
17247

BLISTERTAPE DIMENSIONS in millimeters (inches)



Mat:	A0	B0	K0	W	T	P0	P2	P1	D0	D1	E	F
PS	1.9	4.0	1.5	8.0	0.235	4.0	2.0	4.0	1.5	1	1.75	3.5

Document-No.: S8-V-3717.02-001 (3)

18513



ORIENTATION IN CARRIER TAPE - SMF



Document no.: S8-V-3717.02-003 (4)
Created - Date: 09. Feb. 2010
22670



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[SMF10A-GS18](#) [SMF13A-GS08](#) [SMF7V0A-GS08](#) [SMF20A-GS08](#) [SMF14A-GS08](#) [SMF45A-GS08](#) [SMF6V0A-GS08](#)
[SMF40A-GS08](#) [SMF11A-GS08](#) [SMF6V5A-GS08](#) [SMF15A-GS08](#) [SMF9V0A-GS08](#) [SMF30A-GS08](#) [SMF43A-GS08](#)
[SMF5V0A-GS08](#) [SMF22A-GS08](#) [SMF16A-GS08](#) [SMF33A-GS08](#) [SMF8V0A-GS08](#) [SMF8V5A-GS08](#) [SMF48A-](#)
[GS08](#) [SMF26A-GS08](#) [SMF12A-GS08](#) [SMF7V5A-GS08](#) [SMF51A-GS08](#) [SMF28A-GS08](#) [SMF36A-GS08](#) [SMF24A-](#)
[GS08](#) [SMF18A-GS08](#) [SMF17A-GS08](#) [SMF11A-GS18](#) [SMF12A-GS18](#) [SMF13A-GS18](#) [SMF14A-GS18](#) [SMF15A-](#)
[GS18](#) [SMF16A-GS18](#) [SMF17A-GS18](#) [SMF18A-GS18](#) [SMF20A-GS18](#) [SMF22A-GS18](#) [SMF24A-GS18](#) [SMF26A-](#)
[GS18](#) [SMF28A-GS18](#) [SMF30A-GS18](#) [SMF33A-GS18](#) [SMF36A-GS18](#) [SMF40A-GS18](#) [SMF43A-GS18](#) [SMF45A-](#)
[GS18](#) [SMF48A-GS18](#) [SMF5V0A-GS18](#) [SMF51A-GS18](#) [SMF6V0A-GS18](#) [SMF6V5A-GS18](#) [SMF7V0A-GS18](#)
[SMF7V5A-GS18](#) [SMF8V0A-GS18](#) [SMF8V5A-GS18](#) [SMF9V0A-GS18](#)