









Symmetrical type Silicon Varistors

Parameter Type No.	Absolute Maximum Ratings			DC characteristics					Others	
	I _F (mA)	T _J (°C)	T _{stg} (°C)	V _F (V)		I _F (μA)		R _{th} (j-ℓ)	Mass	Fig.
					I _F (mA)	max	V _F (V)	(°C/W)	(g)	
SV-2SS	150	-40 to +100		4max	100	50	1.2	20	0.3	Ⓐ
SV-3SS	250			2max			0.6			
SV-4SS	150			1.8±0.2	1		0.9			
				2.15±0.2	10					
				2.40±0.25	30					

■ Applications: Divided voltage stabilization circuit, Signal limiter circuit, Temperature detection circuit, Zener voltage stabilization circuit, Meter protection circuit, etc.

SV-2SS, 3SS, 4SS




Type No.	SV-2SS	SV-3SS	SV-4SS
Color indication			
Internal junction			

External Dimensions

(Unit: mm)

Resin molded type
Flammability:
UL94V-0 or Equivalent



● In North America, please send inquiries for the products listed in this page to World Products Inc.