




SEE NOTE 3




PCB LAYOUT RECOMMENDED

TABLE 1

PART NO.	NO. OF POS.	DIMENSIONS	
		A ^{+0.2} _{-0.0}	B ^{+0.1}
WH2D-1/WH2D-1LF	2	7.5	2.5
WH3D-1/WH3D-1LF	3	10.0	5.0
WH4D-1/WH4D-1LF	4	12.5	7.5
WH5D-1/WH5D-1LF	5	15.0	10.0
WH6D-1/WH6D-1LF	6	17.5	12.5
WH7D-1/WH7D-1LF	7	20.0	15.0
WH8D-1/WH8D-1LF	8	22.5	17.5 ^{+0.15} _{-0.10}
WH9D-1/WH9D-1LF	9	25.0	20.0 ^{+0.15} _{-0.10}
WH10D-1/WH10D-1LF	10	27.5 ^{+0.3} _{-0.3}	22.5 ^{+0.15} _{-0.10}
WH11D-1/WH11D-1LF	11	30.0 ^{+0.3} _{-0.3}	25.0 ^{+0.15} _{-0.10}
WH12D-1/WH12D-1LF	12	32.5 ^{+0.3} _{-0.3}	27.5 ^{+0.15} _{-0.10}
WH13D-1/WH13D-1LF	13	35.0 ^{+0.3} _{-0.3}	27.5 ^{+0.15} _{-0.10}

SUFFIX "LF" SEE NOTE 5



NOTES:

1. MATERIAL : NYLON 66, UL94V-0 RATED.
2. ORDERING INFORMATION: SEE TABLE 1
3. FLASH : 0.2 MAX.
4. APPEARANCE : 0.3 MAX.
5. THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS(WAVE SOLDER & SMT)

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		A FCI www.fciconnect.com			
lfr	ecn no	dr	date	linear	.X ±.35	projection		title		WIRE HOLDER 2.5MM PITCH	code
A	T04-0027	M	01/19/04		.XX ±.20						
B	T05-0219	L	09/23/05	angles	.XXX ±.10						
					0° ±2°						
				dr	MAGGIE WU	01/19/04		product family		DIPMATE	sheet -
				engr	LEIF SHEN	01/19/04		size dwg no			
				chr	PAUL WANG	01/19/04					
						scale		A4		JPD22942	sheet 1 of 1
				appr	JOSEPH HSEH	01/19/04	3:1				
sheet	revision	B									
index	sheet	1									