







RECOMMENDED P.C.B. LAYOUT





BOTTOM VIEW



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. ACTUATION FORCE: 300±75gf
5. TRAVEL TO MAKE: 0.3mm +0.4/0.0
6. RATING: 30mA, @12V DC
7. CONTACT RESISTANCE: 50 mΩ—OHMS (Initial)
8. DIELECTRIC STRENGTH: 300 V RMS min at sea level.
9. ELECTRICAL LIFE CYCLE: 150,000 make & break cycles at full load.
10. ▲ DESIGNATE MAJOR DIMENSIONS.
11. OPERATING TEMP: -40°C to +85°C
12. 2002/95/EC (ROHS) COMPLIANT



D	18193	BUTTON LENGTH TOLERANCE CHG.	7/31/08	BLR	E•SWITCH®		
C	15472	REV. DESC, EPOXY LAYOUT	10/28/05	PH			
B	12191	REVISED NOTE 9, ADD NOTE11	5/28/02	CB	GS 10.00 F300 QP		
A	10812	RELEASED FOR PRODUCTION	8/4/00	MM			
REV.	ECN No.	DESCRIPTION	DATE	CHKD	SCALE	DATE	DR
					5:1	7/31/08	MM
							DWG
							REV

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[GS10.00F300QP](#)