


10	9	8	7	6	5	4	3	2	19115
MATERIAL NUMBER	ALTERNATE NUMBER	STUD SIZE	"S" ±.010/0.25	"W" ±.010/0.25	"C" MIN	"L" MAX	"B"	PACKAGING	
191150007	AA-8704-05	5	.126/3.20	.255/6.48	.23/5.8	.81/20.6	.105/2.67	LOOSE PIECE	
191150009	AA-8704-06	6	.140/3.56	.255/6.48	.23/5.8	.81/20.6	.114/2.90		
191150012	AA-8714-08	8	.168/4.27	.310/7.87	.26/6.6	.88/22.2	.139/3.53		
191150014	AA-8715-10	10	.192/4.88	.330/8.38	.26/6.6	.92/23.4	.156/3.96		
191150008	AA-8704-05T	5	.126/3.20	.255/6.48	.23/5.8	.81/20.6	.105/2.67	TAPE MOUNTED	
191150010	AA-8704-06T	6	.140/3.56	.255/6.48	.23/5.8	.81/20.6	.114/2.90		
191150013	AA-8714-08T	8	.168/4.27	.310/7.87	.26/6.6	.88/22.2	.139/3.53		
191150015	AA-8715-10T	10	.192/4.88	.330/8.38	.26/6.6	.92/23.4	.156/3.96		



NOTES:

1. MATERIAL: COPPER

PLATING: ELECTROPLATE TIN

2. FERRULE: TIN-PLATED BRASS

3. INSULATION: LIGHT RED NYLON

4. MWID=MAXIMUM WIRE INSULATION DIA.

5. PARTS ARE ROHS COMPLIANT.

REVISION "L" DIM

EC NO: PG2013-0981

DRWNG: GJAS01

CHKD: JMCNEIL

APPR: JMCNEIL

DATE: 2013/01/02

DATE: 2013/01/31

A2

QUALITY SYMBOLS

▽=0

▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±.005
2 PLACES	±0.13	±.010
1 PLACE	±0.25	±.020
ANGULAR ±1/2°		

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

IN/MM

DRAWN BY	DATE
ETHRODAHL	2010/06/04
CHECKED BY	DATE
JMACNEIL	2010/06/09
APPROVED BY	DATE
JMACNEIL	2010/06/22

MATERIAL NO.

SEE CHART

SIZE

B

SCALE

DESIGN UNITS

INCH

THIRD ANGLE PROJECTION

TITLE

SNAP SPADE TERMINAL AVIKRIMP 22-18 AWG

MOLEX INCORPORATED

DOCUMENT NO.

SD-19115-001

SHEET NO.

1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

tb_frame_B_P_ME_T
Rev. D 2004/04/02