





JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
8102	1.5	.075	.030	0.38	16,000	C-2R
CF23	5.0	.020	.020	0.25	50,000	C-2R
8022	5.0	.021	.034	0.43	10,000	C-2R
7234	5.0	.030	.030	0.38	16,000	C-2R
682	5.0	.060	.030	0.38	100,000	C-2R
685	5.0	.060	.050	0.63	100,000	C-2R
6180	5.0	.060	.150	1.89	5,000	C-2R
714	5.0	.075	.090	1.13	25,000	C-2R
718	5.0	.115	.150	1.89	40,000	C-2R
7240	10.0	.027	.100	1.26	10,000	C-2F
32	12.0	.060	.150	1.89	16,000	C-2F
22	14.0	.040	.150	1.89	16,000	C-2F
8112	14.0	.065	.150	1.89	16,000	C-2F
7241	18.0	.026	.150	1.89	16,000	C-2F
CF16	28.0	.016	.025	0.31	16,000	C-2F
6839	28.0	.024	.150	1.89	16,000	CC-2F



METRIC
DIMENSIONS ARE
IN MILLIMETERS
TOLERANCE UNLESS
OTHERWISE SPECIFIED
1 PL +/- 0.2
2 PL +/- 0
ANGLE +/- 0

JKL

COMPONENTS CORPORATION

TITLE

T-1 STANDARD MIDGET FLANGE

SIZE

A

FSCM NO.

55335

DRAWING NO.

FLANGE T-1

SCALE

NONE

RELEASED DATE

4/5/00

REVISION DATE

9/13/19

REV. NO.

A

SHEET

1 OF 1

DRAWN BY

L. WENGSTROM

APPVD BY DATE

BW 4/5/00

- CAD DRAWING -

MANUAL REVISIONS NOT PERMITTED

REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE
	Ch MOL and Dia to Max dim	9/13/19
	RELEASE & CANCEL 7247, 7231, 7232, CF43, 7250, CF30, CF44, CF45,	4/5/00