

Messrs.					
Product Specification	Model:	NMTG-S12864BFYHSGY-B	Rev. No.	Issued Date.	Page.
			B	Jun. 18, 08	1 / 20

## LCD MODULE SPECIFICATION FOR CUSTOMER'S APPROVAL

**CUSTOMER** : \_\_\_\_\_

**MODULE TYPE** : NMTG-S12864BFYHSGY-B

**APPROVED BY: (FOR CUSTOMER USE ONLY)**

Approved by	Checked by	Made by
 微端 2008/06/18 李剛	 微端 2008/06/18 蔡宜夢	 微端 2008/06/18 陳世文



*Microtips Technology Inc.*

Messrs.					
Product Specification	Model:	NMTG-S12864BFYHSGY-B	Rev. No.	Issued Date.	Page.
			B	Jun. 18, 08	2 / 20

## CONTENTS

ITEM	PAGE
FEATURES	3
LCD MODULE DRAWING	4
GENERAL SPECIFICATION	5
ABSOLUTE MAXIMUM RATING	5
ELECTRICAL CHARACTERISTIC	6
OPTICAL CHARACTERISTIC	6
INTERFACE PIN ASSIGNMENT	7
BLOCK DIAGRAM	10
POWER SUPPLY DIAGRAM	10
TIMING CHARACTERISTICS	11
DISPLAY COMMANDS	13
MEMORY MAPPING	14
ADDRESS CONFIGURATION OF DISPLAY DATA RAM	15
RELIABILITY TEST	16
APPEARANCE CHECK	16
HANDLING PRECAUTIONS	17
LCD PRODUCT QUALITY STANDARD	18
WARRANTY	19
REVISION HISTORY	20



*Microtips Technology Inc.*

Messrs.					
Product Specification	Model:	NMTG-S12864BFYHSGY-B	Rev. No.	Issued Date.	Page.
			B	Jun. 18, 08	3 / 20

**SPECIFICATION FOR**  
**LIQUID CRYSTAL DISPLAY MODULE**  
**MODEL NO. : NMTG-S12864BFYHSGY-B**

View Direction	<input checked="" type="checkbox"/> 6 O'clock		<input type="checkbox"/> 12 O'clock		
LCD Type	<input type="checkbox"/> FSTN Positive			<input type="checkbox"/> FSTN Negative	
	<input type="checkbox"/> STN Gray		<input checked="" type="checkbox"/> STN Yellow Green	<input type="checkbox"/> STN Blue	
Rear Polarizer	<input type="checkbox"/> Reflective		<input checked="" type="checkbox"/> Transflective		<input type="checkbox"/> Transmissive
Backlight Type	<input checked="" type="checkbox"/> LED	<input type="checkbox"/> EL		<input checked="" type="checkbox"/> Internal Power	<input checked="" type="checkbox"/> 5V input
		<input type="checkbox"/> CCFL		<input type="checkbox"/> External Power	<input type="checkbox"/> 24V input
Backlight Color	<input type="checkbox"/> White	<input type="checkbox"/> Amber	<input type="checkbox"/> Blue Green	<input checked="" type="checkbox"/> Yellow Green	<input type="checkbox"/> Other
Temperature Range	<input type="checkbox"/> Normal		<input checked="" type="checkbox"/> Wide		<input type="checkbox"/> Super Wide
EL Driver IC	<input type="checkbox"/> Build-in		<input checked="" type="checkbox"/> Not Build-in		
Touch Screen	<input type="checkbox"/> With		<input checked="" type="checkbox"/> Without		
LCD LSI	SBN640G21 / SBN0064G-D				


**TO BE VERY CAREFUL !**

The LCD driver ICs are made by CMOS process, which are very easy to be damaged by static charge, make sure the user is grounded when handling the LCM.



*Microtips Technology Inc.*

REV.	DESCRIPTION	DRAWN	CHECK	APP'D	DATE
3	2			1	
△	Production release	Addison		Chris Luo	9/11/11
△	Show LED Position	Carol			4/21/04



A Detail  
Scale=4:1



A					
NO.	PART NAME	Q'TY	DATE:	MATERIAL	FINISH
	M-12864BH	1	4/21/04	---	---

PIN ASSIGNMENT									
1.	VDD	5.	DB1	9.	DB5	13.	CS2	17.	E
2.	VSS	6.	DB2	10.	DB6	14.	/RST	18.	FGND
3.	VLC	7.	DB3	11.	DB7	15.	R/W	19.	BKL1
4.	DB0	8.	DB4	12.	/CS1	16.	D/1	20.	BKL2

Messrs.					
Product Specification	Model:	NMTG-S12864BFYHSGY-B	Rev. No.	Issued Date.	Page.
			B	Jun. 18, 08	5 / 20

## GENERAL SPECIFICATION

Item	Content
Display Resolution	128(W)×64(H)
Dimensional Outline(mm)	75.0(W)×52.7(H)×9.0max(D)
Dot Size	0.40(W)mm×0.40(H)mm
Dot Pitch	0.43(W)mm×0.43(H)mm
Display mode	Transflective/ Positive Type
Circuit	Common-Driver IC, Segment-driver IC with build-in SRAM
Interface	Data (D0~D7), D/I, R/W, E, RST, CS1, CS2, V <sub>EE</sub>

## ABSOLUTE MAXIMUM RATING

### (1) Electrical Absolute Ratings

Item	Symbol	Min.	Max.	Unit	Note
Power Supply for Logic	V <sub>DD</sub> -V <sub>SS</sub>	-0.3	7.0	Volt	-
Power Supply for LCD	V <sub>DD</sub> -V <sub>EE</sub>	-0.3	19.0	Volt	-
Input Voltage	V <sub>I</sub>	-0.3	V <sub>DD</sub> +0.3	Volt	-
Current for LED backlight	-	-	200	mA	-
Static Electricity	-	-	--	--	Note 1

Note 1: Operator should be grounded during handling LCM.

### (2) Environmental Absolute Maximum Ratings

Item	Normal Temperature				Wide Temperature			
	Operating		Storage		Operating		Storage	
	Max,	Min.	Max,	Min.	Max,	Min.	Max,	Min.
Ambient Temperature	0°C	+50°C	-20°C	+70°C	-20°C	+70°C	-30°C	+80°C
Humidity(without condensation)	Note 2,4		Note 3,5		Note 4,5		Note 4,6	

Note 2 Ta $\leq$ 50°C: 80% RH max

Ta $>$ 50°C: Absolute humidity must be lower than the humidity of 85%RH at 50°C

Note 3 Ta at -20°C will be <48hrs at 70°C will be <120hrs when humidity is higher than 75%.

Note 4 Background color changes slightly depending on ambient temperature. This phenomenon is reversible.

Note 5 Ta $\leq$ 70°C: 75RH max

Ta $>$ 70°C: absolute humidity must be lower than the humidity of 75%RH at 70°C

Note 6 Ta at -30°C will be <48hrs, at 80 °C will be <120hrs when humidity is higher than 75%.



*Microtips Technology Inc.*

Messrs.							
Product Specification	Model:	NMTG-S12864BFYHSGY-B			Rev. No.	Issued Date.	Page.
		B			Jun. 18, 08		6 / 20

## ELECTRICAL CHARACTERISTICS

Item	Symbol	Condition	Min.	Typ	Max.	Unit	note
Power Supply for Logic	$V_{DD}-V_{SS}$	--	4.5	5.0	5.5	Volt	--
Input Voltage	$V_{IL}$	L level	0	--	0.8	Volt	--
	$V_{IH}$	H level	$V_{DD}-2.2$	--	$V_{DD}$	Volt	--
LCM Recommend LCD Module Driving Voltage	$V_{DD} - V_{EE}$	$T_a = -20^\circ C$	9.14	9.64	10.14	Volt	--
		$T_a = 25^\circ C$	8.60	9.10	9.60		
		$T_a = 70^\circ C$	8.06	8.56	9.06		
Power Supply Current for LCM	$I_{DD}(\text{LED B/L OFF})$	$V_{DD} = 5.0V$ $T_a = 25^\circ C$ $V_{DD}-V_{EE} = 10.3V$ $V_{LED} = 5.0V$	--	1.5	1.8	mA	--
	$I_{EE}$		--	0.6	1.0		
	$I_{LED}$		--	100	150		
Power Supply for EL Backlight	$V_{EL}$		--	100V/ 400Hz	--	--	--

## OPTICAL CHARACTERISTICS

Item	Symbol	Condition	Min.	Typ	Max.	Unit	note
Viewing Angle	Front-Back	$\theta = 0^\circ$	30	92	--	deg.	--
	Left-Right	$\theta = 0^\circ$	60	90	--	deg.	--
Rise Time	$T_r$	$V_{DD}-V_{EE} = 10.3V$ $Ta = 25^\circ C$	--	90	220	mS	--
Fall Time	$T_f$		--	210	200		
Contrast	Cr		2.0	6.0	--	--	7



*Microtips Technology Inc.*

Messrs.					
Product Specification	Model:	NMTG-S12864BFYHSGY-B	Rev. No.	Issued Date.	Page.
			B	Jun. 18, 08	7 / 20



## INTERFACE PIN ASSIGNMENT

Pin No.	Pin Out	I/O	Description
1	V <sub>DD</sub>	-	Logic supply voltage
2	V <sub>SS</sub>	-	GND
3	V <sub>EE</sub>	-	Supply Voltage for LCD panel.
4   11	DB0   DB7	I/O	Data bus. 3-state I/O common terminal.
12	/CS1	I	Chip-select for the left half of the display. Active LOW.
13	/CS2	I	Chip-select for the right half of the display. Active LOW.
14	/RST	I	Setting the RES signal to Low level can initialize the following registers. 1. ON/OFF register 0 set(Display off) 2. Display start line register 0 set(display starts from line 0) After releasing reset, this condition can be changed only by software.
15	R/W	I	Read/Write R/W=high : Data of DB0~DB7 can be read by CPU. R/W=low : Data of DB0~DB7 can be written into LCD driver IC at the falling edge of E when CS1 and CS2 is high.
16	D/I	I	Data/Instruction D/I=high : Indicates that data of DB0~DB7 is display data. D/I=low : Indicates that data of DB0~DB7 is instruction.
117	E	I	Enable When write(R/W=low) : Data of DB0~DB7 is latched at the fall of E When read(R/W=high) : Data is read while E is at high level.
18	FGND	-	Frame Ground
19	BKL <sub>A</sub>	-	Power supply for backlight. (4.2V/100~150 mA DC for LED backlight, 110V/400Hz AC for EL)
20	BKL <sub>K</sub>	-	





*Microtips Technology Inc.*

### [Note 7] Definition of Operation Voltage (Vop)



### [Note 8] Definition of Response Time (Tr, Tf)




#### Conditions:

Operating Voltage : Vop

Frame Frequency : 64 Hz

Viewing Angle( $\theta, \varphi$ ):  $0^\circ, 0^\circ$   
Driving Wave form : 1/N duty, 1/a bias


### [Note 9] Definition of Viewing Direction




*Microtips Technology Inc.*

Messrs.					
Product Specification	Model:	NMTG-S12864BFYHSGY-B	Rev. No.	Issued Date.	Page.
			B	Jun. 18, 08	9 / 20


### [Note 10] Definition of viewing angle



### [Note 11] Description of Measuring Equipment



Reflective type



Transreflective type



*Microtips Technology Inc.*

Messrs.

Product Specification

Model:

NMTG-S12864BFYHSGY-B

Rev. No.

B


Issued Date.

Jun. 18, 08


Page.

10 / 20

## BLOCK DIAGRAM



## POWER SUPPLY



*Microtips Technology Inc.*

Messrs.					
Product Specification	Model:	NMTG-S12864BFYHSGY-B	Rev. No.	Issued Date.	Page.
			B	Jun. 18, 08	11 / 20

## TIMING CHARACTERISTICS

MPU interface timing: ( $V_{SS} = 0V$ ,  $V_{DD} = 4.5V \sim 5.5V$ ,  $T_a = -20$  to  $60^\circ C$ )



Item	Symbol	Min.	Typ.	Max.	Unit
E Cycle Time	$t_C$	1000	--	--	ns
E High Level Width	$t_{WH}$	450	--	--	ns
E Low Level Width	$t_{WL}$	450	--	--	ns
E Rise Time	$t_R$	--	--	25	ns
E Fall Time	$t_F$	--	--	25	ns
Address Setup Time	$t_{ASU}$	140	--	--	ns
Address Hold Time	$t_{AH}$	10	--	--	ns
Data Setup Time	$t_{DSU}$	200	--	--	ns
Data Delay Time	$t_D$	--	--	320	ns
Data Hold Time(Write)	$t_{DHW}$	10	--	--	ns
Data Hold Time(Read)	$t_{DHR}$	20	--	--	ns



*Microtips Technology Inc.*

Messrs.

Product Specification	Model:	NMTG-S12864BFYHSGY-B	Rev. No.	Issued Date.	Page.
			B	Jun. 18, 08	12 / 20



*Microtips Technology Inc.*

Messrs.											
Product Specification			Model:	NMTG-S12864BFYHSGY-B				Rev. No.	Issued Date.	Page.	

## DISPLAY COMMANDS

The display commands shown below control the internal state of the LCD driver ICs. Commands are sent from CPU to LCD module for the display control.

Command	RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0	Function
Display ON/OFF	0	0	0	0	1	1	1	1	1	1/0	To control the display ON or OFF. The internal status and display RAM data are not affected. 0:OFF, 1:ON
Set address (Y address)	0	0	0	1	Y address (0~63)						To set the Y address in the Y address counter.
Set page (X address)	0	0	1	0	1	1	1	Page(0~7)			To set the X address at the X address register.
Display Start Line	0	0	1	1	Display Start Line(0~63)						To indicate the display data RAM displayed at the top of the screen.
Status Read	0	1	Busy	0	ON/OFF	Reset	0	0	0	0	To read status of the LCD controller IC: Busy 0:Ready, 1: In operation ON/OFF: 0:Display ON, 1:Display OFF Reset: 0:Normal, 1:Reset
Write display data	1	0	Write Data						To write data into display data RAM. Y address is increased by 1 after this command.		
Read Display data	1	1	Read Data						To read data from display data RAM to the data bus.		



*Microtips Technology Inc.*

Messrs.									
Product Specification		Model:	NMTG-S12864BFYHSGY-B				Rev. No.	Issued Date.	Page.
								B	Jun. 18, 08 14 / 20

## MEMORY MAPPING

Relationship between RAM data and display

		RAM Y address(Y0 ~Y127)										Data				
1st page(X=0)	Line 0→	0	1	1	1	0	0	.....	0	0	1	0	0	0	←DB0(LSB)	
	Line 1→	1	0	0	0	1	0	.....	0	0	1	1	0	0	←DB1	
	Line 2→	1	0	0	0	1	0	.....	0	0	1	0	1	0	←DB2	
	Line 3→	1	0	0	0	1	0	.....	0	0	1	0	1	0	←DB3	
	...	1	1	1	1	1	1	0	.....	0	0	1	0	0	0	←DB4
		1	0	0	0	1	0	.....	1	1	1	0	0	0	←DB5	
		1	0	0	0	1	0	.....	1	1	1	0	0	0	←DB6	
	Line 7→	0	0	0	0	0	0	.....	0	0	0	0	0	0	←DB7(MSB)	
2nd page(X=1)	Line 8→	1	1	1	1	0	0	.....	0	1	1	1	0	0	←DB0(LSB)	
	Line 9→	1	0	0	0	1	0	.....	0	1	0	0	1	0	←DB1	
	Line 10→	1	0	0	0	1	0	.....	0	1	0	0	1	0	←DB2	
	...	1	1	1	1	0	0	.....	1	1	1	0	1	0	←DB3	
		1	0	0	0	1	0	.....	0	1	0	0	1	0	←DB4	
		1	0	0	0	1	0	.....	0	1	0	0	1	0	←DB5	
		1	1	1	1	1	0	0	.....	0	1	1	1	0	0	←DB6
	Line 15→	0	0	0	0	0	0	.....	0	0	0	0	0	0	←DB7(MSB)	
8th page(X=7)	...	...	...	...	...	...	...	.....	...	...	...	...	...	...		
	Line 56→	1	0	0	0	1	0	.....	0	0	0	0	0	0	←DB0(LSB)	
		1	0	0	0	1	0	.....	0	0	0	0	0	0	←DB1	
	...	1	0	0	0	1	0	.....	0	1	0	0	1	0	←DB2	
		1	1	1	1	1	1	0	.....	1	0	1	0	1	0	←DB3
		1	0	0	0	1	0	.....	1	0	0	1	0	0	←DB4	
		1	0	0	0	1	0	.....	1	0	0	1	0	0	←DB5	
	Line 62→	1	0	0	0	1	0	.....	0	1	1	0	1	0	←DB6	
	Line 63→	0	0	0	0	0	0	.....							←DB7(MSB)	



*Microtips Technology Inc.*

Messrs.				
Product Specification	Model:	NMTG-S12864BFYHSGY-B	Rev. No.	Issued Date.
			B	Jun. 18, 08

## ADDRESS CONFIGURATION OF DISPLAY DATA RAM

		Y address								
		0	1	2	3	.....	126	127		
X=0→	DB0								Line0	
	To								To	
	DB7								Line7	
X=1→	DB0								Line8	
	To								To	
	DB7								Line15	
X=2→	DB0								Line16	
	To								To	
	DB7								Line23	
X=3→	DB0								Line24	
	To								To	
	DB7								Line31	
X=4→	DB0								Line32	
	To								To	
	DB7								Line39	
X=5→	DB0								Line40	
	To								To	
	DB7								Line47	
X=6→	DB0								Line48	
	To								To	
	DB7								Line55	
X=7→	DB0								Line56	
	To								To	
	DB7								Line63	

Address configuration of Display Data RAM



*Microtips Technology Inc.*

Messrs.				
Product Specification	Model:	NMTG-S12864BFYHSGY-B	Rev. No.	Issued Date.
			B	Jun. 18, 08


## RELIABILITY TEST

No	Item	Conditions	Note	
1	High Temp. Operation	70°C	240 Hr	-
2	High Temp. Storage	80°C	240 Hr	-
3	Low Temp. Operation	-20°C	240 Hr	-
4	Low Temp. Storage	-30°C	240 Hr	-
5	High Temp./Humid Storage	60°C 90%RH	240 Hr	-
6	Thermal Shock	-20°C ,30min +60°C ,30min	10 cycles	--
7	Vibration Test ( IEC-68-2-6 )	Frequency : 10~55 Hz Duration : 20 times, 6 min/time Amplitude : 0.75 mm	--	--
8	Shock ( IEC 68-2-27 )	Duration : 11 ms Acceleration : 100g	--	X, Y, Z direction

## APPEARANCE CHECK

### CONDIIION OF APPEARANCE CHECK:

- (1) Specimen shall be checked by eyes in distance of 30cm under 40w-fluorescence lamp.
- (2) Checking direction shall be in 45 degree from perpendicular line op specimen surface.



*Microtips Technology Inc.*

Messrs.					
Product Specification	Model:	NMTG-S12864BFYHSGY-B	Rev. No.	Issued Date.	Page.
			B	Jun. 18, 08	17 / 20

## HANDLING PRECAUTIONS

- (1) Treat polarizer very carefully since it is easy to be damaged.
- (2) When cleaning the display surface, use soft cloth (e.g. gauss) with a solvent (recommended below) and wipe lightly.
  - ◆ ethyl alcohol
  - ◆ iso-prcolol

Do not wipe the display surface with dry or hard materials that will damage the polarizer surface.

Do not use the following solvents:

- ◆ water
- ◆ ketone
- ◆ aromatics

- (3) Direct current causes electro-chemical reaction with remarkable degradation of the display quality. Give careful consideration to prevent direct current at ON/OFF timing and during operation.
- (4) Avoid strong shock and drop from the height.
- (5) To prevent LCD panels from degradation, do not operate or store them exposed directly to sunshine or high temperature/humidity.
- (6) Give careful consideration to avoid electrical static discharge with causes uneven contrast.
- (7) Even a small condensation on the contact pads (terminals) causes electro-chemical reaction which makes missing row and column. Give careful attention to avoid condensation. When assembling with zebra connector, clean the surface of the pads with alcohol and keep the air very clean.



*Microtips Technology Inc.*

Messrs.

Product Specification	Model:	NMTG-S12864BFYHSGY-B	Rev. No.	Issued Date.	Page.
			B	Jun. 18, 08	18 / 20

## LCD PRODUCT QUALITY STANDARD

### DISPLAY APPEARANCE

No	Item	Criteria		
1	inclusions (black spot, white spot, dust)	(1) round type diameter mm(a*) $a \leq 0.20$ $0.20 < a \leq 0.35$ $0.35 < a$ (2) linear type length mm(l) na $l \leq 3$ $3 < l$	no of defect* neglect 5max none width mm(W) $W \leq 0.03$ $0.03 < W \leq 0.08$ $0.08 < W$	no. of defect neglect 6 none
2	scratch	1. scratch on protective film is permitted. 2. scratch on polarizer shall be as follow: (1) round type diameter mm(a*) $a \leq 0.15$ $0.15 < a \leq 0.20$ $0.20 < a$ (2) linear type be judged bye 1.-(2) linear type	no of defect neglect 2 max none	
3	dent	diameter < 1.5mm		
4	bubble	not exceeding 0.5mm average diameter is acceptable between glass and polarizing film		
5	pin hole	$(a+b)/2 \leq 0.15\text{mm}$ maximum number: ignored $0.15 < (a+b)/2 \leq 0.20\text{mm}$ maximum number:10		
6	dot defect	$(a+b)/2 \leq 0.20\text{mm}$ maximum number: ignored $0.20 < (a+b)/2 \leq 0.30\text{mm}$ maximum number:5 x=width		
7	contrast irregularity(spot)	diameter spec $a \leq 0.50\text{mm}$ $0.50 < a \leq 0.75$ $0.75 < a \leq 1.00$ $1.00 < a$	no of defect neglect 5 3 none	
8	dot width	design width $\pm 15\%$		
9	color tone and uniformity	obvious uneven color is not permitted		



*Microtips Technology Inc.*

Messrs.				
Product Specification	Model:	NMTG-S12864BFYHSGY-B	Rev. No.	Issued Date.
			B	Jun. 18, 08

## WARRANTY

This product has been manufactured to your company's specifications as a part for use in your company's general electronic products. It is guaranteed to perform according to delivery specifications. For any other use apart from general electronic equipment, we cannot take responsibility if the product is used in medical devices, nuclear power control equipment, aerospace equipment, fire and security systems, or any other applications in which there is a direct risk to human life and where extremely high levels of reliability are required. If the product is to be used in any of the above applications, we will need to enter into a separate product liability agreement.

- 1 13 months guarantee starts from the date code.
- 2 We cannot accept responsibility for any defect, which may arise from additional manufacturing of the product (including disassembly and reassembly), after product delivery.
- 3 We cannot accept responsibility for any defect, which may arise after the application of strong external force to the product.
- 4 We cannot accept responsibility for any defect, which may arise due to the application of static electricity after the product has passed your company's acceptance inspection procedures.
- 5 We cannot accept responsibility for industrial property, which may arise through the use of your product, with exception to those issues relating directly to the structure or method of manufacturing of our product. Microtips-origin longer than one year from Microtips production.



*Microtips Technology Inc.*

Messrs.					
Product Specification	Model:	NMTG-S12864BFYHSGY-B	Rev. No.	Issued Date.	Page.
			B	Jun. 18, 08	20 / 20

## REVISION HISTORY



# *Microtips Technology Inc.*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microtips Technology:](#)

[NMTG-S12864BFYHSGY-B](#)