


| REV. | DATE     | ECR NO. | DESCRIPTION                            |
|------|----------|---------|----------------------------------------|
| NC   | 02/17/98 | —       | INITIAL RELEASE                        |
| A    | 01/05/06 | —       | UPDATE DRAWING FORMAT                  |
| B    | 12/11/08 | —       | REVISE COUPLING BODY TO SILVER PLATING |
| C    | 03/24/09 | —       | REVISE INTERNAL BODY CONFIGURATION     |



|   |             |                |        |     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |        |                            |                                                                             |          |  |          |
|---|-------------|----------------|--------|-----|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|--------|----------------------------|-----------------------------------------------------------------------------|----------|--|----------|
|   |             |                |        |     | <div>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.</div> <div>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:<br/>0.5 – 8mm ± 0.20mm<br/>8 – 30mm ± 0.40mm<br/>30 – 120mm ± 0.50mm</div> <div>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:<br/>.020 – .315 ± ± 0.007"<br/>.315 – 1.180 ± ± 0.015"<br/>1.180 – 4.724 ± ± 0.020"</div> <div>DO NOT SCALE DRAWING</div> | APPROVALS | DATE   | <div>Amphenol Connex</div> |                                                                             |          |  |          |
| 8 |             |                |        |     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | DRAWN     | GRS    |                            |                                                                             |          |  | 03/24/09 |
| 7 |             |                |        |     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | CHECKED   |        |                            | PART DESCRIPTION<br><div>UHF SOLDER PLUG<br/>(FOR RG-8/U, 11/U CABLE)</div> |          |  |          |
| 6 |             |                |        |     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | ISSUED    |        |                            |                                                                             |          |  |          |
| 5 |             |                |        |     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | SHEET     | 1 OF 1 |                            | PART NO.<br><div>182116</div>                                               |          |  |          |
| 4 | CONTACT PIN | BRASS          | SILVER | 1   | CAD FILE                                                                                                                                                                                                                                                                                                                                                                                                                                                              |           |        |                            |                                                                             |          |  |          |
| 3 | INSULATOR   | BAKELITE BROWN | YELLOW | 1   | C:/182/182116.DWG                                                                                                                                                                                                                                                                                                                                                                                                                                                     |           |        | DWG. NO. 182116.DWG        |                                                                             |          |  |          |
| 2 | BODY        | BRASS          | SILVER | 1   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |        |                            |                                                                             |          |  |          |
| 1 | SHELL       | BRASS          | NICKEL | 1   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |        | REV. C                     | SIZE A                                                                      | SCALE NA |  |          |
|   | DESCRIPTION | MATERIAL       | FINISH | QTY |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |           |        |                            |                                                                             |          |  |          |