



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HM	00		Z	REV ECO-12-020241	26NOV2012	JM	MS



1. DIMENSIONS SHOWN ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
2. CABLE ASSEMBLY SHALL BE WIRED PER WIRING DIAGRAM.
3. MATERIAL:
CONNECTOR HOUSINGS - POLYCARBONATE, UL 94V-0, WHITE.
STRAIN RELIEFS - CARBON STEEL WITH NICKEL PLATING 5.08µm [0.00200] MINIMUM THICK.
CONTACTS - COPPER ALLOY WITH SILVER PLATED STRIP 3.81µm [0.00150] MINIMUM THICK.
4. DIMENSION "A" SHALL BE MEASURED WITH CONDUIT IN THE RELAXED POSITION.
5. DESIGNATIONS IN PARENTHESES () ARE FOR REFERENCE ONLY.
6. MANUFACTURING LOCATION, DATE CODE, PART NUMBER, AND LENGTH SHALL BE INK STAMPED WHERE INDICAED.
7. APPLICATIONS:
AMPINNERGY™ MODULAR WIRING SYSTEM, A MANUFACTURED WIRING SYSTEM.
8. USE GROUND WIRE INSPECTION WINDOW TO VERIFY BONDING AND GROUNDING CONDUCTOR.



4-556212-8	15.24 [50.00]
7-556212-3	12.19 [40.00]
7-556212-2	9.14 [30.00]
4-556212-5	7.62 [25.00]
7-556212-1	6.10 [20.00]
2-556212-3	4.57 [15.00]
3-556212-1	3.05 [10.00]
3-556212-6	1.52 [5.00]
1-556212-5	1.22 [4.00]
3-556212-3	0.91 [3.00]
2-556212-0	0.61 [2.00]
PART NO.	DIM A M [FEET]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. HALL	05MAR01	TE TE Connectivity	
DIMENSIONS: mm[INCHES]		CHK L. SMITH	07MAR01		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD F. LINCOLN	07MAR01	NAME CABLE ASSEMBLY, POWER TO POWER, 5 WIRE	
0 PLC ±°		PRODUCT SPEC		SIZE	
1 PLC ±°		APPLICATION SPEC		CAGE CODE	
2 PLC ±°		WEIGHT		DRAWING NO	
3 PLC ±°		CUSTOMER DRAWING		RESTRICTED TO	
4 PLC ±°		SCALE		SHEET	
ANGLES		1:1		OF	
FINISH		1		REV	
-		Z			